

7-Port USB 3.0 SuperSpeed Hub with BC 1.2 Charging, USB-A

MODEL NUMBER: U360-007



Adds 7 external USB 3.0 ports to your computer, MacBook or Chromebook for connecting hard drives, webcams and other USB devices.

Features

USB 3.0 Hub Adds up to 7 USB Devices to Your Computer, MacBook or Chromebook This 7-port USB 3.0 hub connects directly to the USB-A port on your computer, laptop, MacBook, Surface or Chromebook. It allows you to use as many as seven USB devices, such as flash drives, external hard drives, printers, barcode scanners, webcams, keyboards/mice and power meters, all at the same time. The hub is backward compatible with previous USB standards, so you can also continue using older peripherals while getting maximum performance from current devices.

Supports SuperSpeed USB 3.0 to Ensure Fast Data Transfers and Device Charging The hub supports USB 3.0 SuperSpeed data transfer rates up to 5 Gbps, which is 10 times faster than USB 2.0. It is especially recommended for high-bandwidth USB 3.0 devices, such as security cameras and high-resolution webcams. All seven USB-A ports support USB BC (Battery Charging) 1.2 specifications for fast-charging compatible devices at 5V 2.4A.

Plug-and-Play Hub Comes Ready to Connect Right Away The plug-and-play U360-007 works with Windows and Mac computers and requires no software or drivers to download and install. An external power supply with five-foot cord and NEMA 1-15P plug is included. The hub protects connected devices against overcurrent. An easy-to-see blue LED indicates the unit is providing power.

Sleek and Slim Housing Designed for Everyday Workspace Use or Connecting on the Go The compact unit is designed for convenient positioning within your reach, making USB ports accessible while not taking up much workspace. It is slim enough to pack in your pocket, purse or laptop bag for use in a hotel, conference room or airport.

Highlights

- Adds webcam, flash drive, scanner—up to 7 devices—to your host computer
- USB 3.0 ports support SuperSpeed rates up to 5 Gbps to ensure fast data transfers
- 7 USB-A ports support BC 1.2 specifications for charging mobile devices at 5V 2.4A
- Compact unit works with USB-enabled operating systems, including Windows and Mac
- Plug-and-play operation with no software required for easy, immediate installation

Applications

- Connect up to 7 USB peripherals, such as an external hard drive, MP3 player, power meter and printer, to your MacBook, Chromebook or Surface
- Add easy-to-access USB ports to computers stored in a cabinet, behind furniture or other hard-to-reach location

System Requirements

- Compatible with all USB-enabled operating systems (USB 3.0 port needed to achieve USB 3.0 speeds)

Package Includes

- U360-007 7-Port USB 3.0 SuperSpeed Hub
- USB 3.0 cable, 3 ft.
- External power supply with 5 ft.



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

cord and NEMA 1-15P plug
(Input: 100–240V, 50/60 Hz,
1.5A Max; Output: 12V 3A)

Specifications

OVERVIEW	
UPC Code	037332178480
Product Type	Hub
AC Adapter	Input: 100-240V, 50/60Hz, 0.8A Max / Output: 12V, 2A
Over Current Protection	2.93A
Technology	USB; USB 3.0 (SuperSpeed)
Host Connector	USB A (MALE)
VIDEO	
Number of Monitors Supported	0
Extended Mode	No
Mirror Mode	No
DATA	
Data Ports	(7) USB A (FEMALE)
Data Ports Detail	(7) USB-A - USB 3.2 Gen 1 (5 Gbps)
INPUT	
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240
External Power Supply Plug(s)	NEMA 1-15P North America
Bus Powered	No
Product Length (in.)	6.102
Product Length (cm.)	15.5
Product Length (ft.)	0.508
Product Length (m.)	0.155
POWER	
External Power Supply Input Specs (V / Hz / A)	100-240V / 50/60Hz / 1.5A
External Power Supply Output Specs (V / A)	12V / 3A



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

External Power Supply Cord Length (ft.)	5
External Power Supply Cord Length (m.)	1.5
External Power Supply DC Barrel Connector Specs	OD: 5.5 x 2.5 x 10mm, Positive Pin, Negative Sleeve
External Power Supply Certifications	cUL; RoHS
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Blue (Power)
CHARGING	
Charging Ports / Amps	(1) 2A
Charging Ports	USB-A: 5V 1.5A (7.5W); 2.4A Quick Charge
PHYSICAL	
Color	Black
Material of Construction	ABS
Shipping Dimensions (hwd / cm)	14.00 x 15.01 x 8.99
Shipping Dimensions (hwd / in.)	5.51 x 5.91 x 3.54
Shipping Weight (kg)	0.36
Shipping Weight (lbs.)	0.79
Unit Dimensions (hwd / in.)	0.87 x 6.1 x 2
Unit Packaging Type	Box
Unit Weight (kg)	0.00
Unit Weight (lbs.)	0.00
ENVIRONMENTAL	
Operating Temperature Range	-4 to 158 F (-20 to 70 C)
Storage Temperature Range	-4 to 185 F (-20 to 85 C)
Relative Humidity	20% to 80% RH, Non-Condensing
BTUs	4.8 BTU/Hr
Power Consumption (Watts)	1.4
Power Provided to Connected Device(s)	5V 0.9A (4.5W) Output (USB-A 3.0), 5V 2A (10W) Output (USB 2A Charger)
CONNECTIONS	
Ports	7
Side A - Connector 1	USB 3.0 A (MALE)



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Side B - Connector 1	(7) USB 3.0 A (FEMALE)
Connector Plating	Nickel
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No
STANDARDS & COMPLIANCE	
Certifications	RoHS, FCC, WEEE, EAC
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U360-007](#)