



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

USB-C Cable (M/M) - USB 3.1 Gen 2 (10 Gbps), Thunderbolt 3 Compatible, 3 ft. (0.91 m)

MODEL NUMBER: **U420-003-G2**



Connects and charges USB-C and Thunderbolt 3 devices at USB 3.1 Gen 2 speeds up to 10 Gbps.

Features

Connects and Charges a USB-C or Thunderbolt 3 Device

The three-foot U420-003-G2 connects two devices with USB-C or Thunderbolt 3 ports or connects one device to a USB-C wall charger. This cable supports USB 3.1 Gen 2 data transfer rates up to 10 Gbps and is backward compatible with previous USB generations. Its 3A power output is ideal for fast charging of mobile devices.

Premium Construction Results in Premium Signal Quality

Molded nickel-plated connectors with gold-plated contacts provide maximum conductivity and minimum data loss to guarantee a clear transmission free of interference. Foil and braid shielding delivers reliable, error-free signal quality and protection from EMI/RFI line noise that can distort or destroy data. Integral strain relief gives the cable extra flexibility, reduces stress, and helps the cable move freely without cracking or breaking loose from the connector.

Reversible USB-C Connectors Attach in Either Direction

Unlike traditional USB cables that connect in only one direction, the reversible USB-C male connectors plug into USB-C or Thunderbolt 3 ports in either direction for an instant connection every time.

Highlights

- USB 3.1 Gen 2 data transfer speeds up to 10 Gbps
- Error-free signal quality and EMI/RFI protection
- Compatible with both USB-C and Thunderbolt 3 ports
- Reversible USB-C male connectors on both ends
- Power output up to 3A for fast-charging devices

Package Includes

- U420-003-G2 USB 3.1 Gen 2 Cable, USB-C (M/M), 3 ft.

Specifications

OVERVIEW	
UPC Code	037332197368
Technology	USB 3.1 (Gen 2)
PHYSICAL	
Color	Black
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	5.2MM



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cable Length (ft.)	3
Cable Length (m)	0.9
Cable Length (in.)	36
Material of Construction	PVC
Shipping Dimensions (hwd / cm)	22.86 x 16.51 x 1.27
Shipping Dimensions (hwd / in.)	9.00 x 6.50 x 0.50
Shipping Weight (kg)	0.05
Shipping Weight (lbs.)	0.10
ENVIRONMENTAL	
Operating Temperature Range	14 to 140 F (-10 to 60 C)
Storage Temperature Range	-4 to 185 F (-20 to 85 C)
Relative Humidity	10% to 85% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	USB C (MALE)
Connector Plating	Nickel
Contact Plating	Gold
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.1 Gen 2 (up to 10 Gbps)
STANDARDS & COMPLIANCE	
Certifications	Tested to CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U420-003-G2](#)