

3-Port USB-C Hub with LAN Port, USB-C to 3x USB-A Ports and Gbe, USB 3.0, White

MODEL NUMBER: **U460-003-3AG**



Adds USB-A and Gigabit Ethernet ports to the USB-C or Thunderbolt 3 port on your tablet, laptop, notebook, MacBook, Chromebook, smartphone or PC.

Description

The U460-003-3AG USB 3.1 Gen 1 USB-C Portable Hub/Adapter expands the potential of your tablet, laptop, MacBook, Chromebook, smartphone or PC's USB-C or Thunderbolt 3 port. It's ideal for adding a thumb drive and other USB peripherals, charging a mobile device, and connecting to a Gigabit Ethernet network—all at the same time.

The plug-and-play U460-003-3AG requires no software, drivers or external power. Connect the reversible USB-C plug to your source device's USB-C or Thunderbolt 3 port. The fumble-free USB-C plug connects in either direction to ensure fast, easy connection every time.

Three USB-A ports accept USB peripherals, such as a flash drive, mouse, keyboard or printer, and each provides up to 0.9A for charging smartphones and other mobile devices. All ports support fast USB 3.1 Gen 1 data transfer rates up to 5 Gbps and are backward compatible with previous USB generations, so you can continue using older peripherals while getting high-speed performance from new devices.

The RJ45 port offers access to a Gigabit Ethernet network when no Wi-Fi is available or when a wired connection offers faster speeds. Connect using a UTP cable (sold separately), and enjoy true 10/100/1000 Mbps Ethernet speeds for fast data transfers.

Features

Turn Your Device's USB-C Port into a Multiport Workstation Ideal for adding USB peripherals, powering a mobile device and connecting to a Gigabit Ethernet network simultaneously Plug-and-play operation with no software, drivers or external power required White LED indicates unit is connected and receiving power About the size of a credit card for easy carrying in a pocket, purse or laptop bag

Connect USB Peripherals 3 USB-A ports accept flash drives, mice, keyboards, printers and other USB peripherals Each port provides up to 0.9A for charging mobile devices Supports USB 3.1 Gen 1 data transfer rates up to 5 Gbps Backward compatible with USB 2.0 and USB 1.1

Note: Host must support USB OTG (On-the-Go)

Access a Wired Gigabit Ethernet Network RJ45 port supports true 10/100/1000 Mbps network speeds Recommended for a faster wired network connection or getting online when no Wi-Fi is available

Built-In Cable with Reversible USB-C Connector Fumble-free reversible USB-C plug connects in either direction for quick connection every time

Highlights

- Supports USB 3.1 Gen 1 data transfer rates up to 5 Gbps
- USB-A ports provide up to 0.9A each for charging devices
- Supports true 10/100/1000 Mbps Ethernet network speeds
- Reversible USB-C plug connects in either direction
- Plug-and-play operation with no software or drivers required

System Requirements

- Source device with USB-C or Thunderbolt 3 port

Package Includes

- U460-003-3AG USB 3.1 Gen 1 USB-C Portable Hub/Adapter
- Owner's manual

Specifications



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

OVERVIEW	
UPC Code	037332193803
Product Type	Hub
Technology	Cat5/5e; Cat6; USB 3.0 (SuperSpeed); USB 3.1 (Gen 1); USB
Host Connector	USB C (MALE)
VIDEO	
Number of Monitors Supported	0
Extended Mode	No
Mirror Mode	No
DATA	
Data Ports	(3) USB A (FEMALE)
Data Ports Detail	(3) USB-A - USB 3.2 Gen 1 (5 Gbps)
NETWORK	
Network Ports	RJ45 (FEMALE)
INPUT	
Bus Powered	Yes
Product Length (in.)	6
Product Length (cm.)	15.24
Product Length (ft.)	0.5
Product Length (m.)	0.15
BATTERY	
Battery Charging (5V/1.5A Port)	No
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Green (Power), Orange (Activity)
CHARGING	
Charging Ports / Amps	(3) 0.9A
PHYSICAL	
Color	White
Cable Jacket Rating	VW-1
Material of Construction	ABS, PVC



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Dimensions (hwd / in.)	0.90 x 3.90 x 5.60
Shipping Weight (lbs.)	0.10
Unit Dimensions (hwd / in.)	0.57 x 3.1 x 1.6
Unit Packaging Type	Box
Unit Weight (kg)	0.04
Unit Weight (lbs.)	0.09
ENVIRONMENTAL	
Operating Temperature Range	32 to 113 F (0 to 45 C)
Storage Temperature Range	14 to 158 F (-10 to 70 C)
Relative Humidity	5% to 90% RH, Non-Condensing
BTUs	8.5 BTU/Hr
Power Consumption (Watts)	2.5
Power Provided to Connected Device(s)	5V 0.9A (4.5W) Output per USB port
COMMUNICATIONS	
Network Speed	Gigabit Ethernet (10/100/1000)
IEEE Standards Supported	802.3; 802.3az; 802.3u; 802.3x
CONNECTIONS	
Ports	4
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	(3) USB 3.0 A (FEMALE)
Side B - Connector 2	RJ45 (FEMALE)
Connector Plating	Nickel
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No
UASP Support	Yes
Auto MDIX Support	Yes
Full Duplex Support	Yes
Suspend Mode Support	Yes
Remote Wakeup Support	Yes
STANDARDS & COMPLIANCE	
Certifications	Tested to CE, FCC, RoHS, REACH



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U460-003-3AG](#)