

3-Port USB-C Hub with LAN Port and Power Delivery, USB-C to 3x USB-A Ports and Gbe, USB 3.0, White

MODEL NUMBER: **U460-003-3AG-C**



Adds USB-C PD charging, Gigabit Ethernet and 3 USB-A ports to the USB-C or Thunderbolt 3 port on your MacBook, Chromebook or tablet.

Features

Portable USB 3.1 Hub Turns Your Device's USB-C or Thunderbolt 3 Port into a Workstation This USB-C adapter with Power Delivery (PD) Charging expands the potential of your tablet, laptop, Chromebook, MacBook, smartphone or PC's USB-C or Thunderbolt 3 port. It's ideal for adding a thumb drive and other USB peripherals, powering and charging a PD Charging-compliant mobile device, and connecting to a Gigabit Ethernet network—all at the same time.

PD Charging Port Charges the Connected Chromebook, MacBook Pro or Other Device The USB-C PD charging port provides power and charging to the connected PD Charging-compliant device (such as a MacBook, Chromebook or Android smartphone). Connect the device's AC wall charger to the USB-C PD port, which supports power input up to 20V 3A (60W). That's sufficient wattage to fast-charge, sync and power most high-capacity devices, including the MacBook Pro. Note: USB-C PD port does not support Quick Charge (QC)

Connects USB Peripherals and Transfers Data at Fast USB 3.1 Gen 1 Speeds Three USB-A ports transfer data at speeds up to 5 Gbps, which is 10 times faster than USB 2.0, between your device and up to three USB peripherals, such as a flash drive, printer and keyboard/mouse. The USB Battery Charging (BC) 1.2 port provides power output up to 5V 1.5A (5W) for charging a connected device. The USB ports are backward compatible with previous USB generations, so you can continue using older peripherals while getting high-speed performance from new devices. Note: Host must support USB OTG (On-the-Go)

Accesses a Wired Gigabit Ethernet Network The RJ45 port offers access to a Gigabit Ethernet network when Wi-Fi is unavailable or when a wired connection offers faster speeds. Connect using a UTP cable (Tripp Lite N201-Series Cat6 cables sold separately), and enjoy true 10/100/1000 Mbps Ethernet speeds for fast data transfers.

Reversible USB-C Connector Attaches in Either Direction Unlike traditional USB cables that connect in only one direction, the reversible USB-C male connector plugs into a USB-C or Thunderbolt 3 port in either direction for a fumble-free connection every time.

Ready to Use Right from the Package, So You Can Plug and Play Immediately The plug-and-play USB-C dock is specifically designed for use with the MacBook Pro, Google Chromebook Pixel and other laptops, tablets and devices equipped with a USB-C or Thunderbolt 3 port. It requires no software or drivers. It's smaller than a standard smartphone, making it easy to pack into a pocket, backpack or laptop bag for multipoint convenience wherever you go.

Highlights

- Supports USB 3.1 Gen 1 speeds up to 5 Gbps to ensure fast data transfers
- Power Delivery cable provides 3A (60W) power output for charging connected device
- Connects you to a wired 10/100/1000 Ethernet network when Wi-Fi is unavailable
- Reversible USB-C plug connects in either direction for immediate no-fuss use
- Plug-and-play operation with no software required for easy, immediate installation

Applications

- Save data from your computer to a USB thumb drive or external hard drive
- Access a wired Gigabit Ethernet network in a location with no or spotty Wi-Fi
- Charge your notebook or laptop by connecting its wall charger to the USB-C PD Charging port
- Connect a USB microphone/headset to record a podcast or listen to music
- Write a report using a USB keyboard with your tablet or Android phone

System Requirements

- Source device with USB-C or Thunderbolt 3 port
- Ethernet network with speeds up to 1000 Mbps



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Package Includes

- U460-003-3AG-C USB 3.1 Gen 1 Portable Hub/Adapter
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332193810
Product Type	Hub
Technology	Cat5/5e; Cat6; USB 3.0 (SuperSpeed); USB 3.1 (Gen 1); USB; PD Charging
Host Connector	USB C (MALE)
VIDEO	
Number of Monitors Supported	0
Extended Mode	No
Mirror Mode	No
DATA	
Data Ports	(3) USB A (FEMALE)
Data Ports Details	(3) USB-A - USB 3.2 Gen 1 (5 Gbps)
NETWORK	
Network Ports	RJ45 (FEMALE)
INPUT	
Bus Powered	Yes
Product Length (in.)	6
Product Length (cm.)	15.24
Product Length (ft.)	0.5
Product Length (m.)	0.15
BATTERY	
Battery Charging (5V/1.5A Port)	Yes
POWER	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

USB Power Delivery (PD) Charging Support	Yes
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Green - Power, Orange - Activity
CHARGING	
Total Charging Watts	60
Charging Ports	USB-C: 60W (20V 3A) Power Delivery (PD 2.0); USB-A: 5V 1.5A (7.5W)
Charging Ports / Amps	(1) 1.5A; (1) 3A
PHYSICAL	
Color	White
Cable Jacket Rating	VW-1
Material of Construction	Plastic
Shipping Dimensions (hwd / in.)	5.51 x 0.91 x 3.94
Shipping Weight (lbs.)	0.13
Unit Dimensions (hwd / in.)	0.65 x 3.8 x 1.6
Unit Packaging Type	Box
Unit Weight (kg)	0.04
Unit Weight (lbs.)	0.09
ENVIRONMENTAL	
Operating Temperature Range	32 to 113 °F (0 to 45 °C)
Storage Temperature Range	14 to 158 °F (-10 to 70 °C)
BTUs	8.5 BTU/Hr
Power Consumption (Watts)	2.5
Operating Humidity Range	10 - 85 % RH, Non-Condensing
Storage Humidity Range	5 - 90 % RH, Non-Condensing
Power Provided to Connected Device(s)	Up to 20V 3A (60W) Input (USB-C), 5V 1.5A (7.5W) Output USB port
COMMUNICATIONS	
Network Speed	Gigabit Ethernet (10/100/1000)
IEEE Standards Supported	802.3; 802.3az; 802.3u; 802.3x
CONNECTIONS	
Ports	5
Side A - Connector 1	USB C (MALE)



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Side B - Connector 1	(3) USB 3.0 A (FEMALE)
Side B - Connector 2	RJ45 (FEMALE)
Side B - Connector 3	USB Type-C (FEMALE)
Connector Plating	Nickel
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No
UASP Support	Yes
Auto MDIX Support	Yes
Full Duplex Support	Yes
Suspend Mode Support	Yes
Remote Wakeup Support	Yes
STANDARDS & COMPLIANCE	
Certifications	CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U460-003-3AG-C](#)