



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

## 550VA 300W Line-Interactive UPS - 8 NEMA 5-15R Outlets, AVR, 120V, 50/60 Hz, USB, Desktop/Wall Mount

MODEL NUMBER: AVR550U



Desktop UPS provides battery backup support with automatic voltage regulation (AVR) for your home/office network system or home theater.

### Features

#### 550VA/300W/120V Battery Backup for PCs, Home Theater or Digital Signage

The line-interactive AVR550U UPS system with AVR protection provides reliable battery backup and AC power protection against blackouts, brownouts, overvoltages, surges and line noise that can damage valuable electronics or destroy data. The eight-outlet 120V battery backup is ideal protection for your home office, media center or commerce components, including computers, routers, printers, HDTVs, Blu-ray players, game consoles, ATMs, security systems and digital signage equipment.

#### Allows Time to Back Up Critical Files During a Blackout

Backup support allows you to work through short power failures and gives you enough time to safely save files and shut down your system in case of a prolonged blackout. Backup time varies according to load, but the line-interactive UPS system should keep an energy-efficient desktop computer with small LCD monitor powered as long as 32 minutes. During normal operation, incoming utility power keeps the replaceable internal battery fully charged, so backup power will always be available.

#### 8 NEMA 5-15R Outlets Protect Your Connected Components

Four 5-15R outlets provide battery backup, surge protection and voltage regulation for your computer, monitor and other crucial components. The other four 5-15R outlets provide surge suppression only for printers, speakers and other desktop equipment regarded as non-essential during a blackout. A high >95% line mode efficiency rating reduces BTU emissions, energy consumption and, ultimately, your energy costs.

#### Automatic Voltage Regulation (AVR) Corrects Low- and High-Voltage Conditions

AVR protects your equipment from incremental hardware damage, data loss and performance problems caused by brownouts and overvoltages. The AVR550U can correct brownouts as low as 89V and overvoltages as high as 145V back to nominal 120V power continuously, all while keeping the battery fully charged and ready to take over in case of power failure.

#### 316 Joules Fight Back Against Unexpected Power Surges

A 316-joule surge suppression rating protects connected components from the harmful effects of power surges.

### Highlights

- Protects equipment against blackouts, brownouts, overvoltages, surges and line noise
- Keeps AC power running during blackouts to allow time for file saves and safe shutdown
- 8 NEMA 5-15R outlets power and protect PC, home theater or digital signage equipment
- Home-friendly alarm remains silent in backup mode, sounding only when imperative
- High >95% efficiency with low BTU ratings saves electricity and lowers your energy costs

### Applications

- Protect your PC and other sensitive electronics against power surges, line noise, brownouts, overvoltages and blackouts
- Operate essential equipment during short-term power outages using battery backup power
- Shut down desktop PCs and other equipment without data loss during long-term power outages
- Extend runtime for DVRs, wireless routers and other low-power home network equipment

### Package Includes

- AVR550U 550VA 300W 120V Line-Interactive UPS with 8 Outlets



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

#### Combats Electromagnetic Interference That Can Harm Equipment

Various electromagnetic and radio sources found in virtually every home and business can cause disruptive interference on the AC line. Known as EMI (electromagnetic interference) and RFI (radio frequency interference), this line noise is a common cause of performance problems and can lead to incremental hardware damage, data corruption and audio/video transmission problems. The AVR550U incorporates technology that filters out disruptive line noise so that it won't affect your equipment.

- USB cable
- Owner's manual

#### Home-Friendly Alarm and Diagnostic LEDs Keep You Informed 24/7

The UPS remains silent in both line and battery backup modes. The alarm sounds only to report low battery, battery replace, overload and fault condition. Dual front-panel LEDs report line and battery mode operation.

#### HID-Compliant USB Port Allows for Automatic Saves and Shutdowns

This USB port connects the AVR550U to a computer running Tripp Lite's free downloadable PowerAlert® software to enable safe unattended file saves and system shutdown in case of a prolonged power failure. USB cable is included.

#### Compact Housing Compatible with Easy Desktop or Wall-Mount Installation

The space-saving ABS housing fits on a desktop, shelf or anywhere else convenient to your workstation or home theater. Keyhole mounting tabs on the rear allow easy wall-mount installation. The five-foot power cord with NEMA 5-15P plug connects to any compatible AC outlet.

## Specifications

| OVERVIEW                              |                                     |
|---------------------------------------|-------------------------------------|
| UPC Code                              | 037332211453                        |
| UPS Type                              | Line-Interactive                    |
| INPUT                                 |                                     |
| Rated input current (Maximum Load)    | 6A                                  |
| Nominal Input Voltage(s) Supported    | 120V AC                             |
| UPS Input Connection Type             | 5-15P                               |
| Input Circuit Breakers                | 7A                                  |
| UPS Input Cord Length (ft.)           | 5                                   |
| UPS Input Cord Length (m)             | 1.5                                 |
| Recommended Electrical Service        | 15A 120V                            |
| Input Phase                           | Single-Phase                        |
| OUTPUT                                |                                     |
| Output Volt Amp Capacity (VA)         | 550                                 |
| Output Watt Capacity (Watts)          | 300                                 |
| Nominal Voltage Details               | 120v nominal output in battery mode |
| Frequency Compatibility               | 50 / 60 Hz                          |
| Output Voltage Regulation (Line Mode) | 120V (+6%/-12%)                     |



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

|   |   |
|---|---|
| Output Voltage Regulation (Battery Mode)        | 120V ( $\pm 10\%$ )   |
| UPS Output Receptacles (Surge Suppression Only) | 4 UPS outlets, 4 surge-only outlets   |
| Output AC Waveform (AC Mode)                    | Pure sine wave  |
| Output AC Waveform (Battery Mode)               | PWM sine wave   |
| Nominal Output Voltage(s) Supported             | 110V; 115V; 120V  |
| Output Receptacles                              | (8) 5-15R   |
| Individually Controllable Load Banks            | No  |
| <b>BATTERY</b>                                  |   |
| Battery Type                                    | Valve Regulated Lead Acid (VRLA)  |
| Full Load Runtime (min.)                        | 2 min. (300W)   |
| Half Load Runtime (min.)                        | 9 min. (150W)   |
| Expandable Runtime                              | No  |
| DC System Voltage (VDC)                         | 12  |
| Battery Recharge Rate (Included Batteries)      | 8 hours (10% to 90%)  |
| Battery Access                                  | Battery access door   |
| Internal UPS Replacement Battery Cartridge      | IMPORTANT BATTERY REPLACEMENT INFORMATION > If the original battery inside your AVR550U UPS has a rating of 12V 7AH, please order Tripp Lite <a href="http://www.tripplite.com/UPS-Replacement-Battery-Cartridge-Tripp-Lite-APC-Belkin-Best-Powerware-Liebert-other-UPS-RBC51">RBC51</a> (quantity 1) replacement battery; If the original battery inside your AVR550U UPS has a rating of 12V 3.6AH, please order Tripp Lite <a href="http://www.tripplite.com/UPS-Replacement-Battery-Cartridge-for-Select-Tripp-Lite-AVR550U-AVRX550U-UPS-Systems-12V-RBC36H">RBC36H</a> (quantity 1) replacement battery; If the original battery inside your AVR550U UPS has a rating of 12V 5AH, please contact Tripp Lite for assistance |
| Battery Replacement Description                 | Replaceable internal batteries (see manual)   |
| <b>VOLTAGE REGULATION</b>                       |   |
| Voltage Regulation Description                  | Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 89 to 145  |
| Overvoltage Correction                          | Input voltages between 128 and 145 are reduced by 15%   |
| Undervoltage Correction                         | Input voltages between 89 and 108 are boosted by 18%  |
| <b>USER INTERFACE, ALERTS &amp; CONTROLS</b>    |   |
| Switches  | Power off/on switch   |
| Audible Alarm                                   | UPS remains silent in battery backup mode; Alarm sounds only to report low-battery, fault, overload and replace-battery conditions  |
| LED Indicators                                  | 2 Status LEDs; GREEN indicates power status and operating mode / RED indicates battery-low, overload, replace-battery and fault conditions (see manual)   |
| <b>SURGE / NOISE SUPPRESSION</b>                |   |



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

|   |  |
|---|--|
| UPS AC Suppression Joule Rating                               | 316  |
| UPS AC Suppression Response Time                              | Instantaneous  |
| UPS Dataline Suppression                                      | 1 line TEL/DSL or Ethernet   |
| EMI / RFI AC Noise Suppression                                | Yes  |
| <b>PHYSICAL</b>   |  |
| Installation Form Factors Supported with Included Accessories | Tower; Ultra-compact desktop; Wallmount  |
| Primary Form Factor   | Desktop  |
| Primary UPS Depth (mm)  | 305  |
| Primary UPS Height (mm)                                       | 110  |
| Primary UPS Width (mm)  | 163  |
| Shipping Dimensions (hwd / cm)                                | 15.24 x 23.62 x 37.34  |
| Shipping Dimensions (hwd / in.)                               | 6.00 x 9.30 x 14.70  |
| Shipping Weight (kg)  | 5.95   |
| Shipping Weight (lbs.)  | 13.11  |
| UPS Housing Material  | ABS  |
| UPS Power Module Dimensions (hwd, cm)                         | 11.00 x 16.26 x 30.48  |
| UPS Power Module Dimensions (hwd, in.)                        | 4.33 x 6.4 x 12  |
| UPS Power Module Weight (kg)                                  | 6.21   |
| UPS Power Module Weight (lbs.)                                | 13.7   |
| <b>ENVIRONMENTAL</b>  |  |
| Operating Temperature Range                                   | +32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius  |
| Storage Temperature Range                                     | +5 to +113 degrees Fahrenheit / -15 to +45 degrees Celsius   |
| Relative Humidity   | 0 to 90%, non-condensing   |
| AC Mode BTU / Hr. (Full Load)                                 | 61   |
| AC Mode Efficiency Rating (100% Load)                         | >95%   |
| Operating Elevation (ft.)                                     | Up to 10,000 ft.   |
| Operating Elevation (m)                                       | Up to 3000m  |
| <b>COMMUNICATIONS</b>   |  |
| PowerAlert Software   | For local monitoring via the UPS's built-in communication ports, download PowerAlert Local software at <a href="https://www.tripplite.com/poweralert">https://www.tripplite.com/poweralert</a> |
| Communications Cable  | USB interface cable included   |



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

|   |  |
|---|--|
| WatchDog Compatibility                                      | Supports Watchdog application, OS and hard-reboot restart options for remote applications  |
| Network UPS Tools Compatibility                             | Yes  |
| Communications Interface                                    | USB (HID enabled)  |
| <b>LINE / BATTERY TRANSFER</b>                              |  |
| Transfer Time   | 6 milliseconds typical (10 milliseconds max)   |
| Low Voltage Transfer to Battery Power (Setpoint)            | 89   |
| High Voltage Transfer to Battery Power (Setpoint)           | 145  |
| <b>SPECIAL FEATURES</b>                                     |  |
| Grounding Lug   | Includes side-panel grounding lug  |
| Cold Start (Startup in Battery Mode During a Power Failure) | Cold-start operation supported   |
| High Availability UPS Features                              | Automatic Voltage Regulation (AVR); Surge/noise protection   |
| Green Energy-Saving Features                                | Greater than 95% efficiency - GREEN UPS  |
| <b>STANDARDS &amp; COMPLIANCE</b>                           |  |
| UPS Certifications  | Meets FCC Part 15 Category A (EMI); Tested to CSA (Canada); Tested to NOM (Mexico); Tested to UL1778 (USA)   |
| Certification Details                                       | UL1778: 2014 5th EDITION; CAN/CSA-C22.2 NO. 107.3:2014 3rd EDITION; FCC CLASS A; FCC Part 68 Approved (#5WSWP01B005); Industry Canada Approved (#3449A-005, REN0.1B); RETIE (Colombia) |
| <b>WARRANTY</b>   |  |
| Product Warranty Period (U.S. & Canada)                     | 3-year limited warranty  |
| Product Warranty Period (Latin America)                     | 3-year limited warranty  |
| Product Warranty Period (International)                     | 2-year limited warranty  |
| Product Warranty Period (Mexico)                            | 3-year limited warranty  |
| Connected Equipment Insurance (U.S., Canada & Puerto Rico)  | \$100,000&nbsp;<a class="insuranceLink" href="//www.tripplite.com/support/insurance-policy">Ultimate Lifetime Insurance</a>&nbsp;  |

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[AVR550U](#)