

Administrative management of the KVM is accomplished through the Administration and Security Management 1.2 utility. This is a free download (see the Support Tab at the top of this page) which provides management of user credentials, CAC device management, logs, EDID locking and restoring factory defaults. The Admin and Security Management 1.2 utility is available for Windows only. For managing MAC computers connected to the KVM, settings must be applied through a Windows PC.

## Secure KVM Switch, DVI to DVI - 2-Port, NIAP PP3.0 Certified, Audio, Single Monitor, TAA

MODEL NUMBER: B002-DV1A2



NIAP-certified KVM switch lets you swap between 2 computers with government- and military-level security and data protection.

### Features

**2-Port KVM Switch, DVI to DVI, Is Ideal for Applications That Demand Secure Networks**This 2-port KVM switch is recommended for any government, military, financial or healthcare environment where tight security of sensitive data is of utmost importance in a world of constantly changing cyberthreats. Each KVM port is an electronically isolated channel, making it impossible for data to be transferred between connected computers through the KVM. The single-monitor switch supports crystal-clear HD video resolutions up to 2560 x 1600 (including 1080p) at 60 Hz.

**NIAP PP3.0 Certified to Meet Today's Top Information Assurance Standards**This KVM switch is certified by NIAP (National Information Assurance Partnership), which is operated by the National Security Agency (NSA), to the latest Common Criteria Protection Profile for Peripheral Sharing Switches Version 3.0. Discrete processing paths to each connected system prevent data leakage, transfer and crosstalk between adjacent ports. Peripheral isolation enables data to flow from device to host only.

**Top-of-the-Line Security Features Keep Your Data Safe**Special protection prevents re-programming or reading firmware, so the switch's KVM logic remains unaltered. The keyboard buffer clears automatically after data transmission, ensuring no information is left stored. Plus, you can only access connected computers via buttons on the switch's panel. Other port-switching methods, such as On-Screen Display (OSD) and Hotkey Commands, have been excluded to further ensure data integrity.

**Anti-Tampering Protection Prevents Physical Breaches**If the housing is opened, internal anti-tamper switches will disable the unit, causing it to become inoperable and the front-panel LEDs to flash repeatedly. Seals on the enclosure will provide visual evidence of tampering.

**Maintains Constant Keyboard and Mouse Emulation for Smooth No-Delay Switching**Full USB device filtering ensures support for keyboard and mouse only. This KVM switch also supports secure video emulation and EDID learning, which prevents unwanted data from transmitting through the DDC lines. Both keyboard/mouse and video emulation controllers restrict discovery of newly connected peripherals or monitors during switching operations, shielding your computers from potential vulnerabilities.

**Accessory Cable Kits - P784-006 & P784-010 (Not Included)**Designed specifically for the Tripp Lite B002-DV1A2 and B002-DV1A4 NIAP KVMs, these six-foot cables support DVI video resolutions up to

### Highlights

- Safely and securely switches between 2 isolated computers with different security levels
- Certified to NIAP/Common Criteria Protection Profile for Peripheral Sharing Switches V3.0
- Isolated port paths prevent data leakage between secure and unsecure computers
- Supports HD resolutions up to 2560 x 1600 (@ 60 Hz) for crystal-clear video
- Complies with Federal Trade Agreements Act (TAA) for GSA Schedule purchases

### Applications

- Control up to 2 computers with different security levels from a single monitor/keyboard/mouse
- Protect private information, such as medical or military intelligence data, from cyberattacks

### System Requirements

- DVI monitor
- Wired USB mouse/keyboard with no internal hub or composite device functions (wireless mouse/keyboard not supported)
- Computer with DVI and USB ports
- Computer and speakers with 3.5 mm stereo audio port (optional)
- Windows, Mac, Linux or any



2560 x 1600 (including 1080p) at 60 Hz, as well as USB 2.0 data transfer speeds up to 480 Mbps. By combining three different cables into one convenient cord, you cut down on unnecessary clutter and save money.

**TAA-Compliant for GSA Schedule Purchases**The B002-DV1A2 is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

other major operating system

#### Package Includes

- B002-DV1A2 2-Port NIAP  
PP3.0-Certified DVI-I KVM  
Switch
- External power supply w/NEMA  
1-15P plug & 5 ft. cord (Input:  
100–240V, 50/60 Hz, 0.8A;  
Output: 12V 2A)
- Owner's manual

## Specifications

OVERVIEW	
UPC Code	037332221834
Technology	DVI; USB
VIDEO	
Max Supported Video Resolution	2560 X 1600 @60Hz
INPUT	
Voltage Compatibility (VAC)	100; 110; 125; 127; 200; 208; 220; 230; 240
Redundancy - Dual Power Inputs	No
External Power Supply Plug(s)	NEMA 1-15P North America
POWER	
External Power Supply Input Specs (V / Hz / A)	100-240V / 50/60Hz / 0.8A
External Power Supply Output Specs (V / A)	12V / 2A
External Power Supply Cord Length (ft.)	5
External Power Supply Cord Length (m.)	1.5
External Power Supply DC Barrel Connector Specs	OD: 5.5 x 2.1 x 7.5mm, Positive Pin, Negative Sleeve
External Power Supply Certifications	FCC; UL; cUL
USER INTERFACE, ALERTS & CONTROLS	



LED Indicators	(x2) GREEN / PORT SELECTION, (x2) BLUE / EDID (PUSH-BUTTON), (x1) GREEN / VIDEO CONSOLE
<b>PHYSICAL</b>	
Color	Black
Rackmountable	No
Unit Packaging Type	Box
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32 to 104 F (0 to 40 C)
Storage Temperature Range	4 to 140 F (-20 to 60 C)
Relative Humidity	0% to 80%, Non-Condensing
<b>COMMUNICATIONS</b>	
IP Remote Access	No
<b>CONNECTIONS</b>	
Ports	2
PC/Server Connections	DVI; USB
Side A - Connector 1	3.5MM (FEMALE)
Side A - Connector 2	DVI-I (FEMALE)
Side A - Connector 3	(2) USB A (FEMALE)
Side B - Connector 1	3.5MM (FEMALE)
Side B - Connector 2	DVI-I (FEMALE)
Side B - Connector 3	USB B (FEMALE)
Computer Keyboard and Mouse Interface	USB
Computer Monitor Interface	DVI-I Dual-Link
Console Keyboard and Mouse Interface	USB
Console Monitor Interface	DVI-I Dual-Link
<b>FEATURES &amp; SPECIFICATIONS</b>	
Number of Users	1
NIAP-Certified Secure	Yes
Port Selection	Pushbutton
Common Access Card (CAC) Support	No
Cat5 KVM Switch	No



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	Certified to NIAP PP3.0
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[B002-DV1A2](#)