

2-Port USB/VGA Cable KVM Switch with Cables and USB Peripheral Sharing

MODEL NUMBER: **B032-VU2**



Control 2 computers using one VGA monitor, USB keyboard and USB mouse. Connect a USB 1.1 hub (sold separately) to share USB peripherals, such as printers and hard drives, between computers.

Features

Access and Control 2 Computers with One Keyboard/Mouse/Monitor

- Recommended for home, office and multimedia applications
- Switch between computers using built-in remote port selector
- Supports video resolutions up to 2048 x 1536
- Built-in 3 ft. VGA and USB cables

Independent USB 1.1 Peripheral Sharing

- Adding an optional USB hub (sold separately) to the USB console mouse port allows connection of peripherals, such as printers, hard drives, scanners, webcams and thumb drives

Easy Plug-and-Play Setup and Use

- Compatible with Windows, Mac, Sun and Linux
- No external power supply, software or drivers to install
- Supports most mouse drivers and multifunction mice
- Takes up no valuable desk space

Specifications

Highlights

- Built-in 3-ft. (0.91 m) VGA and USB cables
- Supports video resolutions up to 2048 x 1536
- Supports most mouse drivers and multifunction mice
- Easy remote port switching through built-in selector
- Compatible with Windows®, Mac®, Sun and Linux®

System Requirements

- VGA, SVGA or Multisync monitor
- USB keyboard
- USB mouse
- Computers with VGA and USB ports

Package Includes

- B032-VU2 2-Port USB/VGA Cable KVM Switch
- Owner's manual

OVERVIEW

UPC Code

037332200389



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Max CPU	2
Technology	USB; VGA/SVGA
PHYSICAL	
Shipping Dimensions (hwd / cm)	6.10 x 16.76 x 24.13
Shipping Dimensions (hwd / in.)	2.40 x 6.60 x 9.50
Shipping Weight (kg)	0.41
Shipping Weight (lbs.)	0.90
Unit Dimensions (hwd / cm)	2.59 x 7.9 x 6.6
Unit Dimensions (hwd / in.)	1.02 x 3.11 x 2.6
Unit Weight (kg)	0.30
Unit Weight (lbs.)	0.67
ENVIRONMENTAL	
Operating Temperature Range	32° to 122° F (0° to 50° C)
Storage Temperature Range	-4° TO 140° F (-20° to 60° C)
Relative Humidity	0 to 80% RH, Non-Condensing
COMMUNICATIONS	
IP Remote Access	No
CONNECTIONS	
Ports	2
PC/Server Connections	USB; VGA
Side A - Connector 1	HD15 (FEMALE)
Side A - Connector 2	(2) USB A (FEMALE)
Side B - Connector 1	(2) HD15 (MALE)
Side B - Connector 2	(4) USB A (MALE)
FEATURES & SPECIFICATIONS	
Number of Users	1
NIAP-Certified Secure	No
Cat5 KVM Switch	No
STANDARDS & COMPLIANCE	
Certifications	CE, FCC, RoHS, REACH
WARRANTY	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Product Warranty Period (Worldwide)	3-year limited warranty
--	-------------------------

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[B032-VU2](#)