

Single-Display Monitor Arm with Desk Clamp and Grommet - Height Adjustable, 17" to 32" Monitors

MODEL NUMBER: **DDR1732SC**



Mounts one monitor to your workspace using either clamp or grommet and allows one-touch vertical adjustment via easy-grip knob.

Features

Low-Profile Monitor Desk Mount Makes It Easy to Adjust the Height of Your Monitor Adjusting the height of desktop flat-panel displays at home or the office often requires a lot of effort - loosening fasteners, moving the monitor up and down, tightening knobs to secure the monitor in place. With the Tripp Lite DDR1732SC, all it takes is a simple turn of the easy-grip knob on the back of the vertical support for fast one-touch adjustment from 10.2 to 17.7 inches. The monitor arm is compatible with flat-panel screens ranging from 17 to 32 inches.

Choose Clamp or Grommet Mounting to Match Your Preference This monitor mount includes a clamp for attaching it to the edge of a desk or table and a grommet for secure mounting through the desktop. The clamp supports surfaces ranging from 0.4 to 1 inch thick. Grommet mounting works with surfaces from 0.4 to 1.6 inches thick. Maximum weight capacity is 17.6 lbs (7.9 kgs). Cables are efficiently wrangled through the rear of the arm to keep them organized.

Swivel, Tilt and Rotate the Screen to Find the Perfect and Most Comfortable Viewing Angle This monitor-arm desk mount adjusts independently to optimize viewing angles and improve ergonomics. To minimize screen glare, reduce eye fatigue and increase viewing comfort, the mount features -10° to +10° tilt, 10° swivel and 180° rotation for position your screen in portrait or landscape orientation. Easy screen adjustment lets you quickly find just the right angle without interrupting your workday. The slim design makes this single-monitor mount ideal for sit-stand workstations.

VESA-Compliant Mounting Ensures Display Compatibility VESA (Video Electronics Standards Association) promotes uniformity in the video electronics industry by developing standards for TVs and monitors. For hassle-free display compatibility, this mount supports the following VESA mounting hole patterns: 75 x 75 and 100 x 100. Mounting hardware is included.

Sure to Stand Up to Frequent Use The durable steel frame withstands the stress of repeated adjustments. Its scratch-resistant powder-coated finish tolerates frequent handling and blends easily into any home or office décor.

Highlights

- Low-profile monitor arm attaches to your desktop with either clamp or grommet mount - .4 to 1" for clamp & .4 to 1.6" for grommet.
- One-touch adjustment lets you view the monitor at a comfortable height
- Offers -10° to +10° tilt, 10° swivel and 180° rotation to help you find the perfect angle
- Durable steel construction blends into any décor and supports up to 17.6 lbs (7.9 kgs)
- Display cables attach to slim mount to reduce clutter and keep cords organized

Applications

- Adjust the height of your desk monitor with just a twist of a knob, instead of loosening and tightening multiple fasteners and handles
- Mount a monitor to your sit-stand desk or workstation without taking up much valuable surface space
- Swivel, tilt and/or rotate your screen for the most comfortable viewing angle

Package Includes

- DDR1732SC Single-Display Monitor Arm, 17" to 32" Monitors
- Mounting hardware
- Owner's manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Specifications

OVERVIEW	
UPC Code	037332248893
Device Compatibility	Monitor/HDTV
PHYSICAL	
Color	Black
VESA Pattern (mm)	100x100; 75x75
Degrees of Motion	-10/+10 Tilt and Swivel; 360 Rotate
Material of Construction	Steel
Maximum Screen Size (cm)	81.28
Maximum Screen Size (in.)	32
Maximum Weight Capacity (kg)	8
Maximum Weight Capacity (lbs.)	17.6
Minimum Screen Size (in.)	17
Minimum Screen Size (cm)	43.18
Motion	Swivel; Tilt
Mounting Location	Desk Clamp
Number of Displays	1
Shipping Dimensions (hwd / cm)	40.64 x 12.95 x 8.89
Shipping Dimensions (hwd / in.)	16.00 x 5.10 x 3.50
Shipping Weight (kg)	2.31
Shipping Weight (lbs.)	5.10
Unit Dimensions (hwd / cm)	53.0 x 15.0 x 11.6
Unit Dimensions (hwd / in.)	20.09 X 5.9 X 4.6
Unit Weight (kg)	2.09
Unit Weight (lbs.)	4.6
FEATURES & SPECIFICATIONS	
Tools Necessary	Yes
SPECIAL FEATURES	
Cord Management	Yes
Security Lock	No
STANDARDS & COMPLIANCE	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Approvals	RoHS3, REACH
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[DDR1732SC](#)