

AC/USB Charging Clip for Display Mounts

MODEL NUMBER: **DMACUSB**



Ergonomically friendly space-saving AC and USB charger mounts to your display mount pole to provide easy access to clutter-free device charging.

Description

Ideal for office, hospitality, healthcare, education and any other environments where AC power and USB charging is crucial, the DMACUSB AC/USB Charging Clip attaches to your display mount pole for instant access to clutter-free device charging. The compact all-in-one design fits most display mount poles up to 1.5 inches in diameter for ergonomically friendly power. It features two integrated USB ports (3.4 total amps) for charging your cell phone, tablet and other mobile devices. It also features two NEMA 5-15R outlets for plugging in a laptop docking station and other computer peripherals. No longer will you have to crawl under or reach behind your desk just to plug something in. The removable charge adapter snaps into a holder, which is clamped securely to your display mount pole. Great for traveling, the charge adapter easily unsnaps for providing power on the go. The 6-ft. (1.83 m) power cord with NEMA 5-15P plug reaches nearby wall outlets.

Features

Above-Desk AC and USB Power Solution for Your Home or Office Workstation

- Attaches to monitor's display mount pole with included clamp
- Dual integrated USB-A ports with 3.4A total for charging mobile devices
- Dual integrated NEMA 5-15R outlets for connecting AC-powered peripherals
- Fits most display mount poles up to 1.5 in. diameter
- Snap-out design allows you to take removable charger anywhere
- 6-ft. (1.83 m) power cord with NEMA 5-15P plug reaches nearby wall outlet

Specifications

Highlights

- 2 USB ports with 3.4A total for charging mobile devices
- 2 NEMA 5-15R outlets for connecting peripherals
- Fits most display mount poles up to 1.5 in. diameter
- Snap-out design allows you to take charger anywhere
- 6-ft. (1.83 m) power cord with NEMA 5-15P plug reaches nearby wall outlet

Package Includes

- AC/USB charge adapter
- Adapter holder
- Thumbscrew w/nut
- Clamp
- Rubber pad
- AC power cord w/NEMA 5-15P plug, 6-ft. (1.83 m)
- Owner's manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

OVERVIEW	
UPC Code	037332203458
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V
Input Connection Type	NEMA 5-15P input plug
Input Plug Features	120V, 8A
Voltage Compatibility (VAC)	120
Input Cord Length (ft.)	6
Right-Angle Plug	No
Input Cord Length (m)	1.83
OUTPUT	
Output Receptacles	(2) 5-15R
Circuit Breaker (amps)	8
Right-Angle Outlets	No
CHARGING	
Charging Ports / Amps	(2) 3.4A
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Color	Black
Housing Color	Black
Material of Construction	Plastic
Receptacle Color	Black
Shipping Dimensions (hwd / cm)	10.41 x 17.02 x 9.65
Shipping Dimensions (hwd / in.)	4.10 x 6.70 x 3.80
Shipping Weight (kg)	0.50
Shipping Weight (lbs.)	1.10
Unit Dimensions (hwd / cm)	9.9 x 3.3 x 10.3



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Unit Dimensions (hwd / in.)	3.9 x 1.3 x 4.04
Unit Weight (kg)	0.45
Unit Weight (lbs.)	1
SPECIAL FEATURES	
Cord Management	No
STANDARDS & COMPLIANCE	
Approvals	RoHS
UL1363 (Power Tap)	UL1363
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[DMACUSB](#)