

Keystone Jack Cat6/Cat5e, RJ45, Shielded, Dust Cap, Industrial - 110 Punch Down, IP68, TAA

MODEL NUMBER: N206-KJ01-IND



Connects two Cat5e/6 patch cables in industrial environments that require protection against dust, debris and moisture.

Features

Keystone RJ45 Cat5e Jack Recommended for Outdoor or Harsh Outdoor Environments This Cat6 shielded keystone jack lets you connect two Cat5e/6 patch cables for Gigabit Ethernet networks or digital signage in outdoor applications and other areas where protection from harsh elements is essential. It inserts into an industrial-grade wall plate or surface-mount box to create a watertight seal. An included dust cap protects the shielded RJ45 coupler from dust, debris and moisture when not in use.

IP68 Rating Denotes Resistance to Dust and Water The IP68 rating means the keystone RJ45 Cat5e jack is not only 100% protected against dust, but also able to endure immersion in 1.5 meters of water for up to 60 minutes with no damage or decline in performance, making the kit ideal for basement applications*. For applications that require IP68 protection, we recommend using the keystone jack with a Tripp Lite N206-SB01-IND surface-mount box and N206-Series Cat6 patch cabling. If only IP44 protection against splashing water from all directions is required, we recommend pairing the keystone jack with the N206-Series cable and an N206-FP01-IND, N206-FP02-IND or N206-FP04-IND metal wall plate (all sold separately).

Heavy Shielding Protects Your Network Data from Destructive Line Noise The Cat6 shielded keystone jack fights against EMI/RFI line noise that interferes with your Ethernet or audio/video signal and can distort or destroy data. Electromagnetic interference and radio frequency interference can be created by electric motors, power cables, welding equipment and other heavy machinery frequently found in industrial applications.

TAA-Compliant for GSA Schedule Purchases The N206-KJ01-IND is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

Lifetime Warranty The N206-KJ01-IND is backed by a lifetime warranty, ensuring reliability and performance. **Based on manufacturer's guarantee. Standard IP68 rating guarantees water resistance at depths up to 1.5 meters for up to 30 minutes.*

Highlights

- Built to protect Gigabit Ethernet and digital signage connections in harsh environments
- IP68-rated to resist dust and endure immersion in 1.5 m of water up to 60 min*
- Shielded to protect against EMI/RFI line noise that can destroy data or affect equipment
- Requires 110 punch-down termination to minimize insertion loss for top performance
- Complies with Federal Trade Agreements Act standards for GSA Schedule purchases

**Based on manufacturer's guarantee. Standard IP68 rating guarantees water resistance at depths up to 1.5 meters for up to 30 minutes.*

Applications

- Connect Gigabit Ethernet networks, security cameras or digital signage in factories, warehouses, auto dealerships and garages, and other industrial environments
- Provide Cat6 connectivity in outdoor environments susceptible to rain, such as a stadium or outdoor arena
- Set up outdoor digital signage at malls, theaters and bus stops
- Protect IT infrastructure in basements and other areas susceptible to flooding

Package Includes



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- N206-KJ01-IND Keystone Jack
Cat6/Cat5e, RJ45, Shielded,
Dust Cap, Industrial

Specifications

OVERVIEW	
UPC Code	037332206190
Technology	Cat5/5e; Cat6
PHYSICAL	
Color	Black
Cable Shielding	STP
Shipping Dimensions (hwd / cm)	1.27 x 11.43 x 15.24
Shipping Dimensions (hwd / in.)	0.50 x 4.50 x 6.00
Shipping Weight (kg)	0.09
Shipping Weight (lbs.)	0.20
CONNECTIONS	
Side A - Connector 1	RJ45 (FEMALE)
Side B - Connector 1	RJ45 (FEMALE)
PoE Type	Type 3 PoE++/UPoE (60W, IEEE 802.3bt)
SPECIAL FEATURES	
IP68 Rated	Yes
Snagless Connector	No
STANDARDS & COMPLIANCE	
Certifications	Tested to RoHS, REACH, IP68 (water resistant up to 1.5m depth for 60 minutes based on manufacturer guarantee)
Protection Rating	IP68
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

<https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[N206-KJ01-IND](#)