

MTP/MPO Multimode Base-8 Trunk Cable, 24-Strand, 40GB/100GB, 40/100GBASE-SR4, OM4 Plenum-Rated (3xF/3xF), Push/Pull Tab, Magenta, 11 m (36 ft.)

MODEL NUMBER: **N858-11M-3X8-MG**



Premium multimode fiber optic cabling for transmitting 40/100 Gb data and voice signals. Designed for high-density connections between network equipment in telecom rooms and data centers.

Features

OM4-Rated for 40/100 Gb Ethernet Applications

- Designed to extend high-density connections between network equipment in telecom rooms and data centers
- Recommended for patching between data center MDFs and IDF's
- Optimized for QSFP+ 40GBASE-SR4 and QSFP28 100GBASE-SR4 networks
- Magenta-colored for identification as an OM4 cable

MTP/MPO Connectors with Push/Pull Tabs

- 8-fiber female connectors 12 times denser than SC connectors
- Push/pull tab connectors easy to install and remove with one hand
- 100% tested for low insertion loss and back reflection

Error-Free Signal Transfer

- 50/125 duplex glass fiber construction
- Plenum-rated jacket and bend-insensitive fiber perfect for ceilings, walls and ducts

Specifications

Highlights

- Push/pull tab connectors install/remove with one hand
- 8-fiber MTP/MPO connectors with 12x density of SC connectors
- 100% tested for low insertion loss and back reflection
- 50/125 OM4-rated multimode fiber
- Magenta color for easy OM4 identification

Package Includes

- N858-11M-3X8-MG MTP/MPO Multimode Base-8 Trunk Cable, Magenta, 11 m



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

OVERVIEW	
UPC Code	037332200174
Technology	Multimode; MTP/MPO
Optical Mode	OM4
PHYSICAL	
Cable Jacket Color	Magenta
Clad Diameter	125 micron
Core Diameter	50 micron
Number of Fibers	8
Cable Length (ft.)	36.1
Cable Length (m)	11
Cable Length (in.)	433.1
Shipping Dimensions (hwd / cm)	9.40 x 21.08 x 20.83
Shipping Dimensions (hwd / in.)	3.70 x 8.30 x 8.20
Shipping Weight (kg)	0.68
Shipping Weight (lbs.)	1.50
ENVIRONMENTAL	
Operating Temperature Range	-4 TO 140 F (-20 TO 60 C)
Storage Temperature Range	-4 TO 140 F (-20 TO 60 C)
COMMUNICATIONS	
Network Speed	10Gbps / 40Gbps / 100Gbps
Attenuation @ 850NM	3.0dB/Km
Attenuation @ 1310NM	1.0dB/Km
CONNECTIONS	
Side A - Connector 1	(3) 8-STRAND MTP (FEMALE)
Side B - Connector 1	(3) 8-STRAND MTP (FEMALE)
SPECIAL FEATURES	
Push/Pull Tabs	Yes
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[N858-11M-3X8-MG](#)