

Hospital-Grade Extension Cord, NEMA 5-15P to NEMA 5-15R - Green Dot, 13A, 125V, 16 AWG, 6 ft. (1.83 m), Gray

MODEL NUMBER: P022-006-GY-HG



Hospital-grade extension cord connects two devices with 5-15P-HG/5-15R-HG power connectors in a hospital or other medical facility.

Features

Hospital-Grade Extension Cord is a Safe Solution for Medical Facilities This hospital-grade power cord is designed for computers, mobile carts, printers, scanners, monitors and other compatible hospital equipment within a healthcare facility. It features a NEMA 5-15R-HG end for connecting to a device and a NEMA 5-15P-HG plug for connecting to a hospital-grade AC power source. The 6-ft. (1.83 m) length allows you flexibility in placing equipment with respect to the power outlet.

Designed and Tested to Strict Hospital-Grade Standards This cord is tested to ANSI/UL 62 and 817 standards, as well as CAN/CSA C22.2 no. 21 and 49 standards, ensuring it's a dependable power solution for hospital environments.

Color-Coded to Avoid Misidentification That Can Cause Costly Downtime This extension cord features a gray SJT jacket and fully molded gray ends. The color-coding allows easy, fast identification in a crowded surge protector and helps prevent the cable from becoming inadvertently disconnected.

Highlights

- Adds 6-ft. (1.83 m) to your existing power connection to provide flexibility in placing devices
- Medical power cord replaces or upgrades power cord provided by manufacturer
- 5-15P-HG plug connects to AC power; 5-15R-HG end connects to device's input cord
- Color-coded gray for fast, easy identification in a crowded PDU, UPS or surge protector

Applications

- Connect devices like PCs, mobile carts, monitors and printers to a power outlet up to 6-ft. (1.83 m) away in a hospital environment
- Extend an existing power connection up to 6-ft. (1.83 m) to more easily place a device or reach a power source
- Update or replace the standard power cord provided by a device's original manufacturer

Package Includes

- P022-006-GY-HG Hospital-Grade Extension Cord, 5-15P-HG to 5-15R-HG, 6-ft. (1.83 m), Gray

Specifications

OVERVIEW



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

UPC Code	037332200105
Device Compatibility	Mobile Cart; Computer; Printer; Monitor/HDTV; Server; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	13
Voltage Compatibility (VAC)	125
PHYSICAL	
Color	Gray
Number of Conductors	3
Wire Gauge (AWG)	16
Wire Gauge (OD - mm ²)	1.31
Cable Length (ft.)	6
Cable Length (m)	1.8
Power Cord Jacket Type	SJT
Shipping Dimensions (hwd / cm)	35.99 x 29.97 x 1.27
Shipping Dimensions (hwd / in.)	14.17 x 11.80 x 0.50
Shipping Weight (kg)	0.27
Shipping Weight (lbs.)	0.60
CONNECTIONS	
Side A - Connector 1	NEMA 5-15P-HG
Side B - Connector 1	NEMA 5-15R
SPECIAL FEATURES	
High Voltage	No
Locking Plug	No
STANDARDS & COMPLIANCE	
Certifications	ANSI/UL 62 AND 817, CAN/CSA C22.2 NO. 21 AND 42, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

<https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[P022-006-GY-HG](#)