

## Power Extension Cord, Right-Angle NEMA 5-15P to NEMA 5-15R - Heavy-Duty, 15A, 120V, 14 AWG, 3 ft. (0.91 m), Black

MODEL NUMBER: P024-003-15D



3 ft. extension cord with 5-15R and right-angle 5-15P connectors connects your server to a PDU, UPS, surge protector or wall outlet.

### Features

**Heavy-Duty Extension Cable for Network Devices That Require a Heavy-Gauge Connection** This three-foot extension cord features 14 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. It can be used to connect a computer, server or other device with a NEMA 5-15P plug to a PDU, UPS system, surge protector or wall outlet with a NEMA 5-15R outlet. The three-foot length helps reduce cable clutter and minimize the risk of tripping.

**Right-Angle Plug Makes Connecting in Tight Spaces Easier** The space-saving right-angle NEMA 5-15P connector is easy to install in confined spaces, such as behind your computer desk or workstation. The right-angle construction also relieves strain on the cable and connector and prevents the cable from bending awkwardly.

### Highlights

- Recommended for powering computers, servers and other home/office peripherals
- Right-angle plug allows easier connection in confined or hard-to-reach spaces
- 3-ft. (0.91 m) length allows flexibility in placing devices, while avoiding cable clutter
- Ideal replacement for worn-out or missing 3-ft. (0.91 m) extension cord

### Applications

- Connect devices like computers, servers and monitors to a PDU in your data center
- Extend an existing power connection up to 3 ft. to more easily place a device or reach a power source in a rack
- Provide a high-quality replacement for a worn-out or missing power cord

### Package Includes

- P024-003-15D Heavy-Duty 3-ft. (0.91 m) Extension Cord, Right-Angle NEMA 5-15P to NEMA 5-15R, Black

## Specifications

OVERVIEW	
UPC Code	037332243867
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; UPS; PDU
Country/Region	North America



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

INPUT	
Maximum Input Amps	15
Voltage Compatibility (VAC)	120
PHYSICAL	
Color	Black
Number of Conductors	3
Wire Gauge (AWG)	14
Wire Gauge (OD - mm <sup>2</sup> )	2.08
Cable Length (ft.)	3
Cable Length (m)	0.9
Cable Length (in.)	36
Power Cord Jacket Type	SJT
CONNECTIONS	
Side A - Connector 1	NEMA 5-15P - RIGHT ANGLE
Side B - Connector 1	NEMA 5-15R
SPECIAL FEATURES	
High Voltage	No
Locking Plug	No
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[P024-003-15D](#)