

## DisplayPort to HDMI Active Adapter (M/F) - 4K 60Hz, HDR, DP 1.2, HDCP 2.2, White, 6 in.

MODEL NUMBER: **P136-06N-HDR-W**



4K adapter with HDR support connects an HDMI display to the DisplayPort (DP) 1.2 output on your Chromebook, MacBook or Surface.

### Features

**DisplayPort to HDMI Adapter Connects a 4K HDMI Monitor to Your Computer** Expand the potential of your DisplayPort computer or notebook by connecting it to a 4K HDMI-enabled television, monitor or projector. This active converter helps you transmit digital audio and 4K video from the DisplayPort 1.2 output on your PC, Mac, Chromebook, MacBook, Microsoft Surface or other compatible computer or tablet. It's an ideal tool for working in high-definition photography, videography or cinematography, as well as streaming video for digital signage in crystal-clear 4K.

**More Convenient, Less Expensive Way to Watch 4K Video** This active adapter features a male DP connector and a female HDMI connector, allowing you to continue using your existing HDMI display and HDMI cable (such as Tripp Lite's P568-Series cables) to transmit video signals without the expense of a new DP display.

**Transmits Crystal-Clear 4K HDMI Video with HDR and 4:4:4 Color** The P136-06N-HDR-W supports Ultra HD video resolutions up to 4K at 60 Hz (3840 x 2160). It's compatible with HDMI standards for carrying HDR signals, which provides a wide range of vibrant colors with richer contrast, brighter whites and deeper blacks. HDCP 2.2 compliance allows you to stream iTunes and Netflix content with no complications. This adapter supports 4:4:4 chroma subsampling for top-level PC gaming or using your HDTV as a PC monitor.

**Ready to Use Right from the Package, So You Can Plug and Play Immediately** The plug-and-play DisplayPort to HDMI active converter requires no software, drivers or external power. It's compatible with both Single- and Dual-Mode (DP++) DP output and is recommended for use with graphics cards that do not output DP++ signals. The compact unit fits easily into a briefcase or laptop bag for connecting on the go. The P136-06N-HDR-W is backward compatible with 1080p displays and pre-1.2 DisplayPort sources, allowing you to use the adapter with older equipment.

### Highlights

- Supports UHD resolutions up to 4K @ 60 Hz (4:4:4) for crystal-clear video
- Supports High Dynamic Range (HDR) for richer contrast and expanded color accuracy
- Active adapter converts Single- and Dual-Mode DP++ output for viewing on display
- Compact unit fits easily into pocket, briefcase or laptop bag for instant use anywhere
- Plug-and-play operation with no software required for easy, immediate installation

### Applications

- Watch 4K video content from a DisplayPort-enabled PC, Mac or Surface on an Ultra HD television or projector
- Edit HDR production video or digital photos using a 4K monitor
- Connect a Chromebook or MacBook to a conference table's A/V box to give a video presentation on a large screen
- Upgrade the video quality of your trade show presentation or digital signage installation in a commercial or educational setting to 4K x 2K

### System Requirements

- Source device with DisplayPort output
- Display device with HDMI input



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

#### Package Includes

- P136-06N-HDR-W DisplayPort to HDMI 4K Adapter (M/F), White, 6 in.
- Quick Start Guide

## Specifications

OVERVIEW	
UPC Code	037332241252
Technology	DisplayPort; HDMI; HDR
VIDEO	
Max Supported Video Resolution	4K @ 60 Hz (3840 x 2160)
HDR Support	Yes
3D Video Supported	Yes
Chroma Sub Sampling	4:2:0; 4:2:2; 4:4:4
INPUT	
Built-In Cable Length (ft.)	0.328
Built-In Cable Length (m)	0.1
Built-In Cable Length (in.)	3.94
Built-In Cable Length (cm)	10
Bus Powered	Yes
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	N/A
PHYSICAL	
Color	White
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	4.8mm
Material of Construction	ABS, PVC
Unit Dimensions (hwd / cm)	1.2 x 2.2 x 4.17
Unit Dimensions (hwd / in.)	0.47 x 0.87 x 1.64



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Unit Weight (kg)	0.04
Unit Weight (lbs.)	0.088
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32 to 113 °F (0 to 45 °C)
Storage Temperature Range	14 to 158 °F (-10 to 70 °C)
Operating Humidity Range	10% to 85% RH (No Condensation)
Storage Humidity Range	5% to 90% RH (No Condensation)
<b>COMMUNICATIONS</b>	
EDID Compatible	Yes
Consumer Electronics Control (CEC) Supported	No
<b>CONNECTIONS</b>	
Side A - Connector 1	(1) DISPLAYPORT (MALE)
Side B - Connector 1	(1) HDMI (FEMALE)
<b>FEATURES &amp; SPECIFICATIONS</b>	
Displayport Specification	1.2
HDCP Specification	2.2
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	RoHS, REACH, CE, FCC
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[P136-06N-HDR-W](#)