

## 4K Video and Ethernet 2-in-1 Accessory Kit for Microsoft Surface and Surface Pro with RJ45, DVI, VGA and HDMI Ports

MODEL NUMBER: P137-GHDV-V2-K



Adds Gigabit Ethernet access and an external DVI, VGA or 4K HDMI monitor to your Microsoft Surface or Surface Pro.

### Description

The P137-GHDV-V2-K 4K Video and Ethernet 2-in-1 Accessory Kit expands the capabilities of your Microsoft® Surface® or Surface Pro by adding Gigabit Ethernet access and an external DVI, VGA or 4K HDMI monitor. These two lightweight, low-profile adapters fit neatly into your backpack or laptop bag, so you can use this Microsoft Surface accessory kit anywhere you go.

For displaying videos, spreadsheets, documents and presentations on a larger screen, the Mini DisplayPort™ to DVI/VGA/HDMI adapter has separate DVI-D, HD15 and HDMI female ports for connecting your Surface's Mini DisplayPort to a DVI, VGA or HDMI monitor, television or projector. It supports video resolutions up to 1920 x 1080 (DVI-D); 1920 x 1200, including 1080p (HD15); and 4K x 2K Ultra High Definition up to 3840 x 2160 (HDMI) at 24/30 Hz. It also supports 36-bit Deep Color (12 bits per channel). Only one display can be connected at a time.

The USB 3.0 SuperSpeed to Gigabit Ethernet adapter allows your Surface to access a 10/100/1000 Mbps wired network without an internal Ethernet card. It achieves USB 3.0 data transfer speeds up to 5 Gbps without compromising signal quality. It complies with IEEE 802.3 (10Base-T) and 802.3u (100Base-TX) standards and supports IEEE 802.3az Energy Efficient Ethernet, as well as full- and half-duplex operations, suspend mode and remote wakeup via link-up, and magic packet.

### Features

#### Mini DisplayPort to DVI/VGA/HDMI Adapter

- Connects your Surface to a DVI, VGA or HDMI display
- DVI-D port supports video resolutions up to 1920 x 1080 (1080p)

### Highlights

- Supports HDMI video resolutions up to 3840 x 2160 (4K x 2K) @ 24/30Hz
- Supports VGA video resolutions up to 1920 x 1200 (1080p)
- Supports DVI video resolutions up to 1920 x 1080 (1080p)
- Ensures true 10/100/1000 Mbps Ethernet network speeds
- Small enough to carry easily in laptop bag or backpack

### Package Includes

- Mini DisplayPort to DVI/VGA/HDMI adapter (M/3xF)
- USB 3.0 SuperSpeed to Gigabit Ethernet adapter (M/F)
- Driver CD for Ethernet adapter
- Owner's manual for Ethernet adapter



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

- HD15 port supports video resolutions up to 1920 x 1200, including 1080p
- HDMI port supports UHD video resolutions up to 3840 x 2160 (4K x 2K) @ 24/30 Hz
- Supports 36-bit Deep Color (12 bits per channel)
- Thunderbolt 1 & 2 compatible.

#### USB 3.0 SuperSpeed to Gigabit Ethernet Adapter

- Connects your Surface to a wired Ethernet network
- Ensures true 10/100/1000 Mbps network speeds
- Reaches USB 3.0 data transfer speeds up to 5 Gbps
- Complies with IEEE 802.3, 802.3u, 802.3ab and 802.3az standards
- Supports full- and half-duplex, suspend mode and remote wakeup via link-up, and magic packet

#### Plug and Play Operation

- No external power supply needed
- Small enough to carry easily in laptop bag or backpack
- Compatible with Microsoft Surface and Surface Pro

## Specifications

OVERVIEW	
UPC Code	037332198143
Technology	Cat5/5e; Cat6; DisplayPort; DVI; HDMI; USB 3.0 (SuperSpeed); USB 3.1 (Gen 1); VGA/SVGA
PHYSICAL	
Color	Black; White
Cable Length (ft.)	0.5
Cable Length (m)	0.2
Cable Length (in.)	6
Cable Length (cm)	15.24
Shipping Dimensions (hwd / cm)	2.49 x 13.21 x 15.75
Shipping Dimensions (hwd / in.)	0.98 x 5.20 x 6.20
Shipping Weight (kg)	0.18
Shipping Weight (lbs.)	0.40
CONNECTIONS	
Side A - Connector 1	MINI DISPLAYPORT (MALE)
Side A - Connector 2	USB 3.0 A (MALE)



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Side B - Connector 1	DVI-D DUAL-LINK (MALE) (WIRED TO DVI-D SINGLE-LINK); HD15 (MALE); HDMI (FEMALE)
Side B - Connector 2	RJ45 (FEMALE)
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[P137-GHDV-V2-K](#)