


## M.2 NGFF SATA SSD (B-Key) to 2.5 in. SATA Enclosure Adapter

MODEL NUMBER: **P960-001-M2**



Access an M.2 NGFF SATA SSD (B-Key) drive with a standard SATA computer, SATA drive enclosure or docking station.

### Description

The P960-001-M2 M.2 NGFF SSD to 2.5 in. SATA Enclosure Adapter lets you use an M.2 NGFF SATA SSD (B-Key) drive with a standard SATA-enabled computer, drive enclosure or docking station. To share data, just remove the adapter's cover, connect the drive to the M.2 NGFF connector, secure it with the included screws, put the cover back, and connect the adapter to your computer's SATA port.

The enclosed housing protects the drive when used in applications requiring more durability, such as hot-swap drive bays and external docking stations. The P960-001-M2 supports 2242, 2260 and 2280 M.2 SATA SSD drive types and data transfer rates up to 6 Gbps. It's plug-and-play, so no software, drivers or external power supply are required.

### Features

#### Use an M.2 NGFF SSD as a Standard 2.5 in. SATA SSD

- Access an M.2 NGFF SATA SSD (B-Key) drive with a standard SATA computer, drive enclosure or docking station
- Enclosed housing protects drive in applications requiring more durability
- Supports 2242, 2260 and 2280 M.2 SATA SSD drive types
- Supports data transfer rates up to 6 Gbps (SATA I/II/III)
- Plug-and-play with no software, drivers or external power supply needed

## Specifications

### Highlights

- Supports 2242, 2260 and 2280 M.2 SATA SSD drive types
- Supports data transfer rates up to 6 Gbps (SATA I/II/III)
- Enclosed housing protects drive
- Plug-and-play—no software, drivers or external power supply

### System Requirements

- Supports B-Key and B + M Key M.2 NGFF SATA SSD drives
- Does not support M.2 NGFF PCIe Drives
- SATA host device

### Package Includes

- P960-001-M2 M.2 NGFF SSD to 2.5 in. SATA Enclosure Adapter
- Mounting hardware
- Screwdriver
- Owner's manual



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

OVERVIEW	
UPC Code	037332199256
Drives Supported	2242, 2260, 2280 M.2 NGFF
Technology	SATA/eSATA
PHYSICAL	
Shipping Dimensions (hwd / cm)	2.54 x 12.19 x 15.49
Shipping Dimensions (hwd / in.)	1.00 x 4.80 x 6.10
Shipping Weight (kg)	0.11
Shipping Weight (lbs.)	0.25
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty
Product Warranty Period (U.S. & Canada)	1-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[P960-001-M2](#)