

2.4kW Single-Phase 120V Basic PDU, 13 NEMA 5-15/20R Outlets, NEMA L5-20P Input, 15 ft. (4.57 m) Cord, 1U Rack-Mount

MODEL NUMBER: **PDU1220T**



Highlights

- NEMA L5-20P input with 15-ft. (4.57 m) cord
- 13 NEMA 5-15/20R outlets—12 rear and 1 front
- Switchless design prevents accidental shutdown
- Reversible all-metal housing
- Installs in rack, on wall or under counter

Package Includes

- PDU1220T 2.4kW Single-Phase 120V Basic PDU
- Mounting hardware
- Owner's manual

Delivers 120V single-phase AC power to multiple loads from a utility outlet, generator or UPS system in a high-density IT environment. Ideal for networking, telecom, security, audio/video and sound reinforcement applications.

Description

The PDU1220T 2.4kW Single-Phase 120V Basic PDU is the perfect no-frills unit for networking, telecom, security, audio/video and sound reinforcement applications. Perfectly suited for high-density IT environments, the PDU1220T features a single breakered load bank with 13 NEMA 5-15/20R outlets—12 in the rear and one in front. The NEMA L5-20P input plug with long 15-ft. (4.57 m) cord connects to your facility's compatible AC power source, generator or protected UPS to distribute power to connected equipment.

The switchless design prevents an accidental shutdown, which could lead to costly downtime. A 20A circuit breaker protects connected equipment from dangerous overloads. The reversible all-metal housing mounts in 1U of space in EIA-standard 19-inch racks, as well as on a wall or workbench or under a counter. With a compatible rack and Tripp Lite's PDUSIDEBRKT accessory (sold separately), you can adapt the PDU1220T for vertical 0U rack-mounting.

Features

Reliable Single-Phase Power Distribution

- Ideal no-frills PDU for networking, telecom, security, audio/video and sound reinforcement applications
- 13 NEMA 5-15/20R outlets in one breakered load bank
- 20A circuit breaker protects outlets against overloads
- NEMA L5-20P input plug with 15-ft. (4.57 m) cord
- Rear-panel grounding lug



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Switchless Design

- Prevents accidental shutdowns and costly downtime

Versatile Installation Options

- Mounts horizontally in 1U of EIA-standard 19 in. 2- and 4-post racks
- Reversible all-metal housing faces front or rear in rack
- Ready for toolless 0U vertical installation with optional PDUSIDEBRKT (sold separately)
- Also mounts on wall, workbench or under a counter

Specifications

OVERVIEW	
UPC Code	037332119148
PDU Type	Basic
INPUT	
PDU Input Voltage	120V
Recommended Electrical Service	Single-phase 20A 120V service
Maximum Input Amps	20
PDU Plug Type	NEMA L5-20P
Input Phase	Single-Phase
Input Cord Length (ft.)	15
Input Cord Length (m)	4.57
OUTPUT	
Output Capacity Details	2.4kW (120V) / 20A total capacity; 16A max per 5-15/20R outlet
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(13) 5-15/20R
Output Nominal Voltage	120V
Overload Protection	20A circuit breaker
USER INTERFACE, ALERTS & CONTROLS	
Switches	No power switch
PHYSICAL	
Form Factors Supported	1U rackmount, 0U vertical rackmount, wall-mount and undercounter installation supported
Material of Construction	Metal



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Minimum Required Rack Depth (cm)	24.13
Minimum Required Rack Depth (inches)	9.5
Outlets Measurement (Center to Center)	30.2mm
PDU Form Factor	Horizontal (1U)
Shipping Dimensions (hwd / cm)	23.62 x 5.72 x 51.82
Shipping Dimensions (hwd / in.)	9.30 x 2.25 x 20.40
Shipping Weight (kg)	2.59
Shipping Weight (lbs.)	5.70
Unit Dimensions (hwd / cm)	4.5 x 44.5 x 11.4
Unit Dimensions (hwd / in.)	1.75 x 17.5 x 4.5
Unit Weight (kg)	2.36
Unit Weight (lbs.)	5.2
ENVIRONMENTAL	
Operating Temperature Range	0C ~ 40C (32F ~ 104F)
Storage Temperature Range	-30°C to +50°C (-22°F to +122°F)
Relative Humidity	5 to 95% non-condensing
Operating Elevation (ft.)	0-10,000
Operating Elevation (m)	0-3000
SPECIAL FEATURES	
TVSS Grounding	Back panel grounding lug
STANDARDS & COMPLIANCE	
Certifications	Tested to UL1363 5TH Edition, CAN/CSA-22.2 No. 308-14
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[PDU1220T](#)