

## 1.5kW Single-Phase Hot-Swap PDU, 100-127V 15A Outlets (8 5-15R), 2 5-15P, 10 ft. (3.05 m) & 6 ft. (1.83 m) Cords 2U Rack-Mount

MODEL NUMBER: PDUB15



### Features

- Tripp Lite Hot-swap PDU systems support live-replacement of standard UPS systems for maintenance with no interruption of connected server or networking loads
- PDUB15 is universally compatible with any Tripp Lite or other brand of 100-127V UPS rated up to 1500VA or 1440 watts with a NEMA 5-15P input cable
- 2U horizontal rackmount form factor compatible with 2 or 4 post racks
- Supports space saving rear-post mounting in the same rack space as many Tripp Lite Rackmount UPS systems (select installations, see manual)
- Pair of attached 5-15P PDU input cables connect to separate Utility and UPS power sources
- 8 high quality 5-15R outlets support critical networking loads in both Utility and UPS operating modes
- One additional 5-15R pass-through outlet supports UPS input power cord
- Dual input power cables support PDU connection to separate Utility and UPS power sources
- Manual transfer switch with lighted status indicators controls the source of power to connected equipment between Utility and UPS
- Set the switch to UPS during normal operation and connected equipment will receive full-time conditioned power from the UPS
- Set the switch to Utility to bypass the UPS and provide connected equipment with unfiltered power directly from the Utility line cord while the UPS system is removed and replaced with a fresh one
- Once the new UPS is up and running with all connections restored, set the switch back to the UPS setting to once again provide fully-conditioned UPS power to connected equipment

## Specifications

### Highlights

- Single phase 12A 100-127V Hot-swap PDU
- Enables live replacement of a standard UPS with zero downtime
- 2U horizontal rackmount installation
- Compatible with any 100-127V UPS with a 5-15P input plug
- Manual transfer switch controls PDU input power source
- Pair of 5-15P input cables connect to separate Utility and UPS inputs
- 8 Built-in 5-15R outlets

### Package Includes

- Hot-swap PDU System
- 2U mounting brackets
- User manual with warranty information



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

OVERVIEW	
UPC Code	037332153876
PDU Type	Hot-Swap
INPUT	
PDU Input Voltage	100-127V
Recommended Electrical Service	Works with most 120V UPS systems up to 1500VA
Maximum Input Amps	12
PDU Plug Type	NEMA 5-15P
Input Cord Length Details	Utility input cable (10 ft / 3m) / UPS input cable (6 ft / 1.8m)
Input Phase	Single-Phase
OUTPUT	
Output Watt Capacity (Watts)	1440
Output Capacity Details	1.52kW (127V), 1.44kW (120V), 1.2kW (100V) / 15A total capacity (Agency de-rated to 12A); 12A max per 5-15R outlet
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(8) 5-15R
Output Nominal Voltage	100-127V
Overload Protection	n/a
USER INTERFACE, ALERTS & CONTROLS	
Front Panel LEDs	Lighted indicators confirm UPS and Utility switch position and operating mode
Switches	Manual 2 position transfer switch offers fast switching between UPS and Utility operating modes in less than 6 milliseconds
PHYSICAL	
Form Factors Supported	2U rackmount in 2 or 4 post racks
Material of Construction	Metal
PDU Form Factor	Horizontal (2U)
Shipping Dimensions (hwd / cm)	31.24 x 15.75 x 50.80
Shipping Dimensions (hwd / in.)	12.30 x 6.20 x 20.00
Shipping Weight (kg)	4.04
Shipping Weight (lbs.)	8.90
Unit Dimensions (hwd / cm)	8.7 x 44 x 7.7
Unit Dimensions (hwd / in.)	3.42 x 17.32 x 3.03
Unit Weight (kg)	3.49



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Unit Weight (lbs.)	7.70
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	0C ~ 40C (32F ~ 104F)
Storage Temperature Range	-30°C to +50°C (-22°F to +122°F)
Relative Humidity	5-95% non condensing
Operating Elevation (ft.)	0-10,000
Operating Elevation (m)	0-3000
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	Tested to UL60950 (USA), CSA (Canada)
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[PDUB15](#)