

# 1.4kW Single-Phase Metered PDU, 120V Outlets (16 5-15R), 5-15P, 15 ft. (4.57 m) Cord, 0U Vertical, 48 in.

MODEL NUMBER: PDUMV15



## Features

- 15A single phase 120V Metered Power Distribution Unit / PDU (Agency de-rated to 12A continuous)
- Two-digit lighted meter reports combined total output current in amps
- Attached NEMA 5-15P 15A 120V input plug with 15-ft. (4.57 m) line cord
- 0U 48in / 122cm vertical rackmount format installs using no rack spaces
- 16 NEMA 5-15R outlets
- Includes 15A circuit breaker and lighted power switch inside a transparent protective cover
- Toolless installation supported in button-mount compatible equipment racks
- Bolt-down installation brackets support installation in other racks and additional surfaces

## Specifications

OVERVIEW	
UPC Code	037332132536
PDU Type	Metered
INPUT	
PDU Input Voltage	120V
Recommended Electrical Service	Single-phase 15A 120V service
Maximum Input Amps	12
Maximum Input Amps Details	Agency de-rated to 12A continuous

## Highlights

- Metered single phase 12A 120V 0U 48in / 122cm vertical rackmount PDU
- Two-digit current meter reports output current in amps
- Attached 15-ft. (4.57 m) cord with NEMA 5-15P input plug
- 16 NEMA 5-15R outlets
- Toolless button mount and bolt-down bracket installation hardware included

## Package Includes

- PDUMV15 Metered Vertical PDU
- Mounting hardware and spare mounting buttons
- Owner's manual with warranty information



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

PDU Plug Type	NEMA 5-15P
Input Phase	Single-Phase
Input Cord Length (ft.)	15
Input Cord Length (m)	4.57
<b>OUTPUT</b>	
Output Capacity Details	1.44kW (120V) / 12A total capacity; 12A max per outlet
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(16) 5-15R
Output Nominal Voltage	120V
Overload Protection	15A circuit breaker
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Front Panel LCD Display	Digital meter reports PDU output current in amps
Switches	Lighted on/off switch with transparent switch cover
<b>PHYSICAL</b>	
Form Factors Supported	Vertical (0U) mounting in rack enclosures
Material of Construction	Metal
PDU Form Factor	Vertical (0U)
Shipping Dimensions (hwd / cm)	131.50 x 8.71 x 6.10
Shipping Dimensions (hwd / in.)	51.77 x 3.43 x 2.40
Shipping Weight (kg)	2.01
Shipping Weight (lbs.)	4.43
Unit Dimensions (hwd / cm)	123.1 x 3.81 x 4.2
Unit Dimensions (hwd / in.)	48.47 x 1.5 x 1.64
Unit Weight (kg)	1.70
Unit Weight (lbs.)	3.74
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	0C ~ 40C (32F ~ 104F)
Storage Temperature Range	-30°C to +50°C (-22°F to +122°F)
Relative Humidity	5-95% Non-condensing
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	Tested to UL 60950-1: 2007 R10.14 (USA), CAN/CSA-C22.2 No. 60950-1-07+A1:2011+A2:2014 (Canada), RoHS Compliant



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[PDUMV15](#)