



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

UL1363a, Paragraph 14.1(d) States "The SPRPT shall be permanently attached to the medical equipment by a means such that it is only removable with the use of a tool." To achieve compliance, one must use the PSCLAMP.

Safe-IT UL 1363A Medical-Grade Power Strip for Patient-Care Vicinity, 6x 15A Hospital-Grade Outlets, Safety Covers, 7 ft. Cord

MODEL NUMBER: PS-607-HG-OEM



Supplies power to movable plug-connected components mounted to IV poles, mobile carts, crash carts and mobile medical workstations in operating rooms and patient-care vicinities.

Description

The PS-607-HG-OEM Medical-Grade Power Strip supplies power to movable plug-connected components mounted to a rack, table or pedestal in operating rooms, patient-care vicinities, therapy rooms, imaging environments and administrative areas. Compliant with UL 1363A specifications, this 120V, 50/60 Hz power strip features a NEMA 5-15P-HG hospital-grade plug and six NEMA 5-15R-HG hospital-grade outlets that include integrated locking safety covers.

The power strip is protected by a patented antimicrobial powder coating with EPA-registered and FDA-compliant silver ionic technology. The antimicrobial surface protection is 99.9 percent effective in inhibiting the growth of bacteria and reducing the risk of HAIs in hospitals and other medical environments. The coating meets the requirements of JIS Z 2801:2000, an international standard for evaluating efficacy in antimicrobial products.

Two built-in resettable 15A circuit breakers control power to all outlets and protect the power strip against overloads. Switchless design prevents the unit from being accidentally shut off. The seven-foot (2.1 m) power cord provides ample reach to the AC power source.

Mounting tabs and flanges let you install the PS-607-HG-OEM on a wide variety of surfaces, such as IV poles, mobile carts, crash carts and mobile medical workstations. The all-metal housing ensures safety and is guaranteed to last a long time in demanding environments.

Features

Power Distribution Anywhere in Any Medical Facility Ideal for use in operating rooms, patient-care vicinities, therapy rooms, imaging environments and administrative areas For use on IV poles, mobile carts, crash carts and mobile workstations, when properly mounted 120V, 50/60 Hz power strip complies with UL 1363A specifications

Exclusive, Patented Antimicrobial Protection Silver ionic powder coating is 99.9% effective in inhibiting the growth of bacteria Patented coating helps to reduce the risk of healthcare-acquired infections (HAIs) in

Highlights

- Patented antimicrobial coating is 99.9% effective in inhibiting the growth of bacteria
- Approved for use in patient-care vicinities when properly mounted
- Complies with UL 1363A specifications
- 6 NEMA 5-15R-HG outlets with integrated locking safety covers
- 7 ft. (2.1 m) cord with NEMA 5-15P-HG plug reaches nearby outlets

Package Includes

- PS-607-HG-OEM UL 1363A Medical-Grade Power Strip, 7-ft. (2.13 m) cord
- Owner's manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

hospitals and other medical environments Coating meets the requirements of JIS Z 2801:2000, an international standard for evaluating efficacy in antimicrobial products.

Versatile Medical-Grade Solution 6 NEMA 5-15R-HG hospital-grade outlets provide consistent power 7-ft. (2.13 m) power cord with NEMA 5-15P-HG hospital-grade plug provides ample reach to the power source Rugged, all-metal housing for long life in demanding environments

Premium Safety Features Integrated locking outlet safety covers block access to unused outlets Dual resettable built-in 15A circuit breakers protect against dangerous overloads Switchless design prevents accidental shutoff

Ready to Use Right Out of the Box Built-in mounting tabs and flanges for easy installation on a variety of surfaces

Specifications

OVERVIEW	
UPC Code	037332203649
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A, 120V
Input Plug Features	Hospital Grade Plug
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P-HG
Input Cord Length (ft.)	7
Input Cord Length (m)	2.13
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(6) 5-15R-HG
Circuit Breaker (amps)	15
Overload Protection	2 x 15amp breaker (1 line, 1 neutral)
Transformer Accommodation	(2) Yes
Outlet Orientation	Single row of 6
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Switches	No power switch
PHYSICAL	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Color	White
Antimicrobial Coating	Yes
Power Cord Color	White
Form Factors Supported	IV poles, mobile carts, crash carts and mobile medical workstations
Housing Color	White
Included Mounting Accessories	Mounting tabs and flanges
Integrated Keyhole Mounting Slots	Yes (Includes flanges)
Material of Construction	Metal
Outlets Measurement (Center to Center)	38.7mm
Receptacle Color	White
Shipping Dimensions (hwd / cm)	5.59 x 14.48 x 36.58
Shipping Dimensions (hwd / in.)	2.20 x 5.70 x 14.40
Shipping Weight (kg)	1.59
Shipping Weight (lbs.)	3.50
Unit Dimensions (hwd / cm)	34.93 x 6.35 x 3.81
Unit Dimensions (hwd / in.)	13.75 x 2.5 x 1.5
Unit Weight (kg)	1.09
Unit Weight (lbs.)	2.40
SPECIAL FEATURES	
Built-in Cable Management	No
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[PS-607-HG-OEM](#)