


Protect It! 8-Outlet Home Computer Surge Protector, 8 ft. (2.43 m) Cord, 1080 Joules, Space-Saving Plug

MODEL NUMBER: SK6-6



Highlights

- 8 outlets / 8-ft. (2.43 m) cord
- 1080 joule rating

Package Includes

- SK6-6 Surge Suppressor
- Child Safety Covers
- Color-coded cord identifiers
- Warranty information and Instruction manual

Description

The SK6-6 Surge Suppressor from Tripp Lite has 8 outlets and an 8-ft. (2.43 m) cord with a space-saving right-angle plug. The unit has 1080 joules of surge energy absorption to handle the strongest surges. Diagnostic LEDs alert the user to potential power problems. \$35,000 Ultimate Lifetime Insurance (USA and Canada Only). The SK6-6 comes with child safety covers and color-coded cord identifiers.

Features

- 8 outlets with child safety covers
- 8-ft. (2.43 m) cord with space-saving right-angle plug
- \$35,000 Ultimate Lifetime Insurance (USA and Canada Only) covers connected equipment -
- Surge energy absorption: 1080 joules; 54,500 amps
- 15 amp circuit breaker
- 3 diagnostic LEDs indicate AC present, grounded & protection present
- EMI/RFI noise filtering
- Keyhole supports for wall mounting
- Recessed and lighted power switch
- Color-coded cord identifiers

Specifications

OVERVIEW	
UPC Code	037332010018



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	8
Right-Angle Plug	Yes
Input Cord Length (m)	2.44
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(8) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(3) Yes
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Switches	Two position red illuminated on/off power switch
Diagnostic LED Details	PROTECTION PRESENT (green), GROUNDED (red) and LINE OK (green)
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1080
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	140
AC Suppression Surge Current Rating	54,500 amps
UL1449 Let Through Rating	400V - UL Verified
Immunity	Conforms to IEE 587 / ANSI C62.41
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Network (Ethernet) Protection	No
PHYSICAL	
Antimicrobial Coating	No
Power Cord Color	Light Gray
Housing Color	Light Gray
Integrated Keyhole Mounting Slots	Yes
Keyhole Slot Mounting Measurement (Center to Center)	114.3mm
Material of Construction	Plastic
Outlets Measurement (Center to Center)	28.6mm
Receptacle Color	Light gray
Shipping Dimensions (hwd / cm)	36.58 x 3.81 x 14.22
Shipping Dimensions (hwd / in.)	14.40 x 1.50 x 5.60
Shipping Weight (kg)	0.82
Shipping Weight (lbs.)	1.80
Unit Dimensions (hwd / cm)	3.8 x 6.4 x 33
Unit Dimensions (hwd / in.)	1.5 x 2.5 x 13
SPECIAL FEATURES	
Rotatable Outlets	No
STANDARDS & COMPLIANCE	
Canada	cUL
Approvals	Exceeds IEEE 587 category A&B specifications
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition
UL1363 (Power Tap)	UL1363
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$35,000 Ultimate Lifetime Insurance

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[SK6-6/SPIKEBAR](#) [SK6-0/SPIKEBLOK](#)