

Protect It! Surge Protector with 6 Right-Angle Outlets, 6 ft. (1.83 m) Cord, 540 Joules, Diagnostic LED

MODEL NUMBER: **SPIKESTIK**



Highlights

- 6 right-angle outlets
- 6-ft. (1.83 m) cord
- 540 joule rating

Package Includes

- SPIKESTIK Surge Suppressor
- Child Safety Covers
- Instruction manual and Warranty information

Description

The SPIKESTIK Surge Suppressor from Tripp Lite has 6 right-angle outlets and a 6-ft. (1.83 m) cord. The unit has 540 joules of surge energy absorption to handle the strongest surges.

Features

- 6 right-angle outlets
- 6-ft. (1.83 m) cord
- Surge energy absorption: 540 joules; 27,000 amps
- 15 amp circuit breaker
- EMI/RFI noise filtering
- Keyhole supports for wall mounting
- \$20,000 Ultimate Lifetime Insurance (U.S., Canada & Puerto Rico only)
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required

Specifications

OVERVIEW	
UPC Code	037332010292
INPUT	
Nominal Input Voltage(s) Supported	120V AC



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Recommended Electrical Service	120V (110-125V)
Voltage Compatibility (VAC)	120
Maximum Surge Amps	36000
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	6
Right-Angle Plug	No
Input Cord Length (m)	1.83
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(3) Yes
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Switches	Two position on/off power switch
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	540
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	150
AC Suppression Surge Current Rating	27,000 amps
UL1449 Let Through Rating	400V - UL Verified
EMI / RFI Filtering	Yes
Immunity	Conforms to IEE 587 / ANSI C62.41
Automatic Shut-Off	Yes
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

PHYSICAL	
Antimicrobial Coating	No
Power Cord Color	Light Gray
Housing Color	Light Gray
Integrated Keyhole Mounting Slots	Yes
Keyhole Slot Mounting Measurement (Center to Center)	114.6mm
Material of Construction	Plastic
Outlets Measurement (Center to Center)	28.6mm
Receptacle Color	Light gray
Shipping Dimensions (hwd / cm)	30.23 x 4.44 x 1.78
Shipping Dimensions (hwd / in.)	11.90 x 1.75 x 0.70
Shipping Weight (kg)	0.59
Shipping Weight (lbs.)	1.30
Unit Dimensions (hwd / cm)	26 x 6.9 x 3.9
Unit Dimensions (hwd / in.)	10.25 x 2.70 x 1.52
SPECIAL FEATURES	
Rotatable Outlets	No
STANDARDS & COMPLIANCE	
Canada	cUL
Approvals	Exceeds IEEE 587 category A&B specifications
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition
UL1363 (Power Tap)	UL1363
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$20,000 Ultimate Lifetime Insurance

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[SPIKESTIK](#)