

SmartRack 6U Low-Profile Switch-Depth-Plus Wall-Mount Mini Rack Enclosure, Wide, Acrylic Window

MODEL NUMBER: **SRW6UDPGVRT**



6U rack cabinet with extra width for convenient cable management houses, organizes and secures standard 19 in. rack equipment.

Features

Space-Saving 6U Wall-Mount Enclosure Houses 19 in. Rack Equipment up to 20.5 in. Deep This SmartRack® cabinet is designed to house 6U of equipment, such as network switches and patch panels. It's recommended for network wiring closets, retail locations, classrooms, back offices and other areas with limited floor space where you need equipment to be secure, organized and out of the way. Constructed from heavy-duty steel with a durable black powder-coated finish, the cabinet has a maximum load capacity of 200 lbs (90.7 kgs).

Lockable for Simple and Secure Equipment Access The front door and side panels lock securely to help prevent damage, tampering or theft. The reversible front door can open left or right by rotating the cabinet 180 degrees before mounting. Convenient top and bottom access ports allow easy cable routing through the cabinet.

Generous Airflow Keeps Equipment Cool Round ports built into the top, bottom and both sides are designed for optional ventilation fans (such as Tripp Lite's SRFANWM, sold separately) that keep your equipment cool and functioning at their peak.

Designed with Extra Width for Easier Cable Access and Better Airflow The SRW6UDPGVRT is three inches wider than Tripp Lite's standard-width wall-mount racks. Combined with two vertical cable managers with pre-installed finger ducts in front and two cable pass-through ports on top, the extra width provides convenient cable management along the front of the rack. This allows easier cable access from the front and increases airflow by minimizing rear cable clutter that can obstruct vents. Cutouts on top of the rack can be used to secure cable bundles.

Shatter-Resistant Clear Acrylic Front Window The front door features a shatter-resistant clear acrylic window that lets you monitor equipment readouts without unlocking the enclosure. Not only does the window help prevent equipment tampering and reduce acoustic noise, it also adds visual flair to your IT installation.

Easy Enclosure and Equipment Installation This 6U server rack comes fully assembled and ready to mount to the wall with user-supplied hardware. The side panels can be removed for convenient installation, maintenance and replacement of equipment. Square and threaded mounting holes and numbered rack spaces make equipment installation easy. Front and rear mounting rails adjust independently to accommodate equipment up to 20.5 inches deep, including network switches and patch panels.

Meets Payment Card Industry Standards The SRW6UDPGVRT provides physical equipment and media security required for PCI DSS (Payment Card Industry Data Security Standard) compliance.

Highlights

- 6U rack constructed from powder-coated steel that stands up to tough environments
- Doors and side panels lock securely to help prevent damage, tampering or theft
- Extra 3 in. width and internal cable managers cut down on rear cord clutter
- Ships fully assembled for immediate wall-mounting with user-supplied hardware
- Provides physical equipment and media security required for PCI DSS compliance

Applications

- Store and organize rack-mount equipment in a network wiring closet, retail location, classroom, office or other area where you need equipment to be secure

Package Includes

- SRW6UDPGVRT SmartRack 6U Low-Profile Switch-Depth-Plus Wall-Mount Rack Enclosure Cabinet
- (22) M6 screws
- (22) M6 cage nuts
- (22) M6 cup washers
- (22) 12-24 screws
- Removable mounting plate
- Vertical cable management fingers
- (3) Mounting plate screws
- (2) Keys
- Owner's manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Specifications

OVERVIEW	
UPC Code	037332214256
Device Compatibility	Patch Panel; Network Switch; UPS
Rack Type	Enclosure
PHYSICAL	
Color	Black
Maximum Device Depth (cm)	52.07
Maximum Device Depth (in.)	20.5
Maximum Device Depth (mm)	521
Minimum Device Depth (cm)	7.62
Minimum Device Depth (in.)	3
Minimum Device Depth (mm)	76
Cable Access Hole Measurement (inches)	9.812 x 2.35 (l x w)
Rack Height	6U
Shipping Dimensions (hwd / in.)	17.72 x 24.40 x 32.28
Shipping Weight (kg)	22.68
Unit Dimensions (hwd / cm)	37.01 x 75.23 x 55.14
Unit Dimensions (hwd / in.)	14.58 x 29.62 x 21.71
Unit Weight (kg)	20.18
Unit Weight (lbs.)	44.5
Weight Capacity - Stationary (kg)	91
Weight Capacity - Stationary (lbs.)	200
Rack Depth	Shallow
Number of Vertical Mounting Rails	4
SPECIAL FEATURES	
Grounding Lug	Front and Back door frames
Built-in Cable Management	Yes
STANDARDS & COMPLIANCE	
Certifications	EIA-310-E; IP20 Protection Rating
Approvals	RoHS



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[SRW6UDPGVRT](#)