

SmartRack 16U Low-Profile Vertical-Mount Wall-Mount Half-Height Server Rack Enclosure

MODEL NUMBER: **SRWF16U38**



Wall-mount cabinet secures and organizes 16U of 19-in. rack equipment in network wiring closets and other locations with limited floor space. Houses equipment up to 35 in. deep, but extends just 24 in. from wall.

Description

The SRWF16U38 SmartRack® 16U Low-Profile Vertical-Mount Server-Depth Wall-Mount Rack Enclosure Cabinet is designed to house EIA-standard 19-inch rack equipment in network wiring closets, retail locations, classrooms, back offices, two-post racks and other areas with limited floor space where you need equipment to be secure, organized and out of the way. Constructed from heavy-duty steel with a durable black powder-coated finish, the cabinet has a maximum load capacity of 400 lbs (181.4 kgs).

Because the low-profile cabinet mounts vertically, it extends only 24 inches from the wall while housing equipment up to 35 inches deep, including 1U servers, UPS systems, battery packs and switches. In addition to 12U of rack space in the primary mounting area, it also includes a 4U mounting space at the top of the enclosure for patch panels.

The top cover and front panel are removable to allow expedient access to equipment. The cover also locks securely with the included keys to help prevent damage, tampering or theft. The vented cabinet allows air to flow freely and keep equipment cool. Convenient top, bottom and side ports allow easy cable routing.

The SRWF16U38's modular design allows you to disassemble the cabinet in minutes for wall-mounting with user-supplied hardware. Mounting holes are spaced 16 inches apart to accommodate standard wall studs. Equipment installation is easy with threaded mounting holes that support 12-24 mounting in two-post racks.

Features

Highlights

- Maximum load capacity of 400 lbs (181.4 kgs)
- Locking steel cabinet vented to keep equipment cool
- Secures 12U of 19 in. rack equipment up to 35 in. deep
- Includes additional 4U of space for patch panels
- Modular design for easy disassembly and assembly

Package Includes

- SRWF16U38 SmartRack 16U Low-Profile Vertical-Mount Server-Depth Wall-Mount Rack Enclosure Cabinet
- (2) Keys
- Owner's manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Saves Valuable Workspace

- Recommended for areas with limited floor space where you need equipment to be secure, organized and out of the way
- Houses EIA-standard 19 in. rack equipment in 12U of space
- Also includes 4U of mounting space at the top of the enclosure for patch panels
- Extends only 24 in. from the wall while housing equipment up to 35 in. deep
- Maximum load capacity of 400 lbs (181.4 kgs)

Keeps Important Equipment Secure

- Top cover locks securely to help prevent damage, tampering or theft
- Vented cabinet keeps equipment cool
- Convenient ports with removable covers allow cable routing through top, bottom and sides

Easy Enclosure and Equipment Installation

- Modular design for easy disassembly and assembly
- Wall-mounting holes spaced 16 in. apart for standard wall stud placement
- Threaded mounting holes support 12-24 mounting in 2-post racks
- Rack spaces marked for easy reference

Meets Payment Card Industry Standards

- Provides physical equipment and media security required for PCI DSS (Payment Card Industry Data Security Standard) compliance

Specifications

OVERVIEW	
UPC Code	037332195869
Device Compatibility	Network Switch; Patch Panel; Server
Rack Type	Enclosure
PHYSICAL	
Color	Black
Maximum Device Depth (cm)	88.90
Maximum Device Depth (in.)	35
Maximum Device Depth (mm)	889
Rack Height	16U
Shipping Dimensions (hwd / cm)	122.00 x 78.99 x 43.00
Shipping Dimensions (hwd / in.)	48.03 x 31.10 x 16.93



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Weight (kg)	45.81
Shipping Weight (lbs.)	101.00
Unit Dimensions (hwd / cm)	96.52 x 50.01 x 58.9
Unit Dimensions (hwd / in.)	38 x 19.69 x 23.19
Unit Weight (kg)	36.97
Unit Weight (lbs.)	81.5
Weight Capacity - Stationary (kg)	181
Weight Capacity - Stationary (lbs.)	400
Rack Depth	Standard
Number of Vertical Mounting Rails	2
SPECIAL FEATURES	
Built-in Cable Management	No
Extra Wide	No
STANDARDS & COMPLIANCE	
Certifications	EIA-310-E; IP20 Protection Rating
Approvals	RoHS
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[SRWF16U38](#)