

## Wall-Mount Roof Fan Kit - Dual 230V High-Performance Fans, 210 CFM, 3 ft. (0.91 m) Cord, C14 Input

MODEL NUMBER: **SRXFANWM**



Increases airflow inside wall-mount rack enclosures to keep equipment cool, boost system performance and avoid costly downtime.

### Features

**Increase Ventilation Inside Your Wall-Mount Rack Enclosures and Server Cabinets** Tripp Lite's SRXFANWM SmartRack® Wall-Mount Roof Fan Kit is an ideal accessory for maintaining a constant flow of air within your rack enclosures and server cabinets. Better airflow keeps your valuable rack components cool, helps boost system performance and avoids costly equipment failures that can lead to downtime, damage and data loss.

**Powerful 230V Fans Provide Proper Cooling** Two durable five-inch 230V fans mount inside or outside the cabinet to draw hot exhaust air out and facilitate equipment cooling. The high-performance fans circulate air at 210 cubic feet per minute (CFM) and do so quietly at about 50 decibels—about as loud as your refrigerator.

**Compatible with Tripp Lite SmartRack Wall-Mount Enclosures** The SRXFANWM comes fully assembled and ready to mount to your rack cabinet with the included hardware. Compatible racks include SRW6U, SRW9U, SRW10US, SR12UB, SRW12U, SRW12US, SRW12US33, SRW12USG, SRW18US, SRW26US and other Tripp Lite SmartRack enclosures that specify the use of this accessory. The three-foot AC power cord features a C14 input plug that connects to a conveniently located wall outlet, surge protector or PDU.

### Highlights

- Cools rack equipment to boost system performance and avoid costly downtime
- High-performance 5 in. 230V fans draw warm air up through rack at 210 CFM
- 50 dB sound rating ensures quiet operation—about as loud as your refrigerator
- Includes hardware for mounting inside or outside standard 19 in. rack cabinets
- 3-ft. (0.91 m) power cord with C14 input connects to conveniently located AC outlet

### Applications

- Draw warm air away from rack-mounted equipment to boost system performance, prevent costly downtime and extend operating life

### System Requirements

- SRW6U, SRW9U, SRW10US, SR12UB, SRW12U, SRW12US, SRW12US33, SRW12USG, SRW18US, SRW26US and other Tripp Lite SmartRack enclosures that specify the use of this accessory

### Package Includes

- (2) 230V high-performance fans
- (2) Fan guards
- Rack-mounting hardware
- Owner's manual



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

## Specifications

OVERVIEW	
UPC Code	037332243195
INPUT	
Nominal Input Voltage(s) Supported	230V AC
Nominal Input Voltage Description	230V 50 Hz
Input Plug Features	C14
Input Cord Length (ft.)	3
Input Cord Length (m)	0.91
COOLING	
Cooling Type	Passive
PHYSICAL	
Shipping Dimensions (hwd / in.)	3.10 x 7.80 x 11.60
Shipping Weight (kg)	1.77
Unit Dimensions (hwd / cm)	Por Ventilador 13.21 x 13.21 x 4.1
Unit Dimensions (hwd / in.)	5.20 x 5.20 x 1.61
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[SRXFANWM](#)