


Protect It! 230V 6-Universal Outlet Surge Protector, 1.8M Cord, British Plug, 750 Joules

MODEL NUMBER: **SUPER6OMNIB**



Highlights

- 6 universal outlets
- 1.8 m power cord with British plug
- 750 joule rating
- Lighted on/off switch with integrated circuit breaker

Package Includes

- SUPER6OMNI B AC surge suppressor
- Instruction manual and warranty information

Description

Tripp Lite's Protect It!™ SUPER6OMNI B offers economical AC surge suppression for full protection of 220-250V workstations, desktop PCs, telecom systems and other sensitive electronics. Built-in AC surge suppression shields connected equipment from damage and performance problems due to transient surges. The SUPER6OMNI B offers 6 universal outlets and a 1.8 meter AC line cord with a British plug. AC suppression rated at 750 joules shields equipment from surges and line noise. Internal shutters also offer additional protection. Lighted on/off switch with integrated circuit breaker provides power control over connected equipment. Right-angle outlets keep connected cords from blocking adjacent outlets. Attractive light gray high-impact housing.

INPUT: 1.8 m AC line cord with British plug

OUTPUT: 6 universal receptacles

ELECTRICAL: 220-250V AC, 50/60Hz, 10A

FORMAT: Corded multi-outlet strip

SUPPRESSION: - AC: 750 joules

Features

- Protect It!™ SUPER6OMNI B offers economical AC surge suppression
- 750 joules AC surge suppression shields equipment from surges and line noise
- 6 universal outlets protect computers and peripherals
- Internal shutters provide additional safety
- 1.8 m AC line cord with British plug
- Built-in power switch and 10 amp circuit breaker offers power control and overload protection over all outlets
- Fail-safe thermal fusing protects against fire and other damage in the event of an extreme, extended overvoltage or surge condition



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- Attractive light gray high-impact housing with keyhole mounting tabs allow versatile placement options
- Right-angle outlets keep connected cords from blocking adjacent outlets

Specifications

OVERVIEW	
UPC Code	037332121158
INPUT	
Nominal Input Voltage(s) Supported	230V AC
Recommended Electrical Service	230V (220-250V)
Voltage Compatibility (VAC)	220-250
Maximum Surge Amps	13500
Input Plug Type	British
Input Cord Length (ft.)	6
Right-Angle Plug	No
Input Cord Length (m)	1.83
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(6) Universal outlets
Circuit Breaker (amps)	10
Overload Protection	10A resettable illuminated combo switch/circuit breaker
Outlet Orientation	right-angled
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	No
Switches	Two position power switch
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	750
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G/H-G) line surge suppression
Automatic Shut-Off	No



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Antimicrobial Coating	No
Power Cord Color	Black
Housing Color	Light Gray
Integrated Keyhole Mounting Slots	Yes
Keyhole Slot Mounting Measurement (Center to Center)	219.5mm
Material of Construction	Plastic
Outlets Measurement (Center to Center)	51mm
Receptacle Color	Light gray
Shipping Dimensions (hwd / cm)	5.33 x 11.18 x 42.67
Shipping Dimensions (hwd / in.)	2.10 x 4.40 x 16.80
Shipping Weight (kg)	0.64
Shipping Weight (lbs.)	1.40
Unit Dimensions (hwd / cm)	39.4 x 6.4 x 3.2
Unit Dimensions (hwd / in.)	15.50 x 2.50 x 1.25
Unit Weight (kg)	0.45
Unit Weight (lbs.)	1.0
SPECIAL FEATURES	
Rotatable Outlets	No
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[SUPER6OMNI B](#)