

## Protect It! 10-Outlet Surge Protector, 6 ft. Cord, 2880 Joules, Black Housing

MODEL NUMBER: TLP1006B



Safeguard your PC, printer, scanner, router, modem and other home electronics against dangerous surges, spikes and line noise. Recommended for home, office, workstations, dorms and hotel rooms.

### Description

Perfect for your home or office workstation, the TLP1006B Protect It!® 10-Outlet Surge Protector features a surge protection rating of 2880 joules to defend your sensitive electronic components against strong surges and spikes. In fact, Tripp Lite will repair or replace any connected equipment damaged by surges up to \$100,000 for life (valid in the U.S., Canada and Puerto Rico only).

The TLP1006B includes full normal mode (H-N) and common mode (N-G/H-G) line surge suppression, as well as technology that filters out EMI/RFI line noise, preventing interference from disrupting your electronics and inflicting damage or data loss.

Your computer and peripherals plug into 10 NEMA 5-15R outlets that are spaced apart to accept bulky transformers without blocking adjacent outlets. Safety covers keep dust and debris away from unused outlets. Integrated 15A circuit breaker protects all outlets and shuts down connected equipment in case of overload. On/off switch provides one-touch control over connected equipment. Diagnostic LED bars indicate power and protection status.

The six-foot (1.8-meter) AC power cord with right-angle NEMA 5-15P plug allows furniture and equipment to be placed flush against the wall. Keyhole slots incorporated into the bottom panel provide convenient wall or desk mounting options for the black plastic housing.

### Features

**2880-Joule Surge Protection for Home or Office Electronics** Protects your computer, printer, scanner, external hard drive and other sensitive electronics against even the strongest surges and spikes

Recommended for home, office, workstations, dorms and hotel rooms  
 Full normal mode (H-N) and common mode (N-G/H-G) line surge suppression  
 Filters out disruptive EMI/RFI line noise that can cause equipment damage or data loss  
 Exceeds IEEE 587 Category A and B surge suppression specifications

**10 Outlets Accept Wide Range of Electronic Devices** 10 NEMA 5-15R AC outlets accept most computers and peripherals  
 Outlets spaced widely apart to accept bulky transformers

**Premium Safety Features** On/off switch provides one-touch control over connected equipment  
 Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required  
 Diagnostic LED bars show power and protection status at a glance  
 Safety covers protect unused outlets from dust and debris

**Fits Effortlessly Into Your Workstation** 6 ft. AC power cord with right-angle NEMA 5-15P plug allows furniture and equipment to be placed flush against the wall  
 Keyhole slots on bottom panel provide

### Highlights

- 10 widely spaced NEMA 5-15R outlets
- 2880-joule surge protection rating
- Filters out threatening EMI/RFI line noise
- 15A resettable circuit breaker prevents dangerous overloads
- 6 ft. AC power cord with right-angle NEMA 5-15P plug

### Package Includes

- TLP1006B Protect It! 10-Outlet Surge Protector, Black Housing
- Owner's manual



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

convenient wall or desk mounting options Black plastic housing designed for long life  
**Backed by Tripp Lite's Ultimate Lifetime Insurance** \$100,000 Ultimate Lifetime Insurance covers any connected components damaged by power surge (U.S., Canada and Puerto Rico only)

## Specifications

OVERVIEW	
UPC Code	037332200013
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	6
Right-Angle Plug	Yes
Input Cord Length (m)	1.83
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	60 Hz
Output (Watts)	1800
Output Receptacles	(10) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(10) Yes
Right-Angle Outlets	Yes
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	2880
AC Suppression Response Time	< 1ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
UL1449 Let Through Rating	330,400,400
EMI / RFI Filtering	Yes
Immunity	Conforms to IEE 587/ANSI C62.41
Automatic Shut-Off	Yes



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Antimicrobial Coating	No
Power Cord Color	Black
Housing Color	Black
Integrated Keyhole Mounting Slots	Yes
Material of Construction	Plastic
Receptacle Color	Black
Shipping Dimensions (hwd / cm)	4.06 x 22.10 x 34.54
Shipping Dimensions (hwd / in.)	1.60 x 8.70 x 13.60
Shipping Weight (kg)	0.96
Shipping Weight (lbs.)	2.12
SPECIAL FEATURES	
Rotatable Outlets	No
STANDARDS & COMPLIANCE	
Approvals	RoHS
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition, UL1363
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$100,000&nbsp;<a class="insuranceLink" href="//www.tripplite.com/support/insurance-policy">Ultimate Lifetime Insurance</a>&nbsp;

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[TLP1006B](#)