

## USB-A to RJ45 Rollover Console Cable (M/M) - Cisco Compatible, 250 Kbps, 15 ft. (4.57 m), Black

MODEL NUMBER: **U009-015-RJ45-X**



Rollover console cable connects your computer or laptop's USB-A port to a serial-based Cisco device with a console port.

### Features

**Ideal for IT Pros Who Need a Connection Between Computer and Cisco Console Device** This rollover cable is designed for consumers or IT professionals who want a reliable connection between their computer or laptop's USB-A port and a Cisco modem, router, firewall, switch or other serial-based Cisco device with a console port. The cable works with both older and new Cisco models, supporting data transfer rates up to 250 Kbps.

**Top-Quality Construction for Top-of-the-Line Performance** No extra software or external power is required to use this 15-ft. (4.57 m) cable. Premium double shielding eliminates crosstalk and reduce EMI/RFI line noise that can disturb your electronics and inflict hardware damage or data loss. The U009-015-RJ45-X works with Windows, Mac and Linux operating systems.

### Highlights

- Great for programming, resetting or rebooting a Cisco switch, firewall, router or modem
- 15-ft. (4.57 m) cable supports data transfer speeds up to 250 Kbps
- Double-shielded construction cuts crosstalk and EMI/RFI line noise
- Plug-and-play operation with no software required for easy, immediate installation
- Compatible with Windows, Mac and Linux

### Applications

- Program, reset or reboot a serial-based Cisco switch, firewall, router or modem through its console port

### System Requirements

- Computer or laptop with USB-A port
- Serial-based Cisco device with console port

### Package Includes

- U009-015-RJ45-X USB to RJ45 Rollover Console Cable (M/M), Black, 15-ft. (4.57 m)

## Specifications

OVERVIEW	
UPC Code	037332222121
Technology	USB



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

POWER	
USB Power Delivery (PD) Charging Support	No
PHYSICAL	
Color	Black
Cable Outer Diameter (OD)	5.5mm; 4.7mm +/- 0.15
Cable Jacket Material	PVC
Wire Gauge (AWG)	26
Cable Length (ft.)	15
Cable Length (m)	4.57
Cable Length (in.)	180
Material of Construction	PVC, PE
Cable Length (cm)	457
Unit Packaging Type	Polybag
Unit Weight (kg)	0.18
Unit Weight (lbs.)	0.3968
ENVIRONMENTAL	
Operating Temperature Range	32 to 104°F (0 to 40°C)
Storage Temperature Range	-4 to 140°F (-20 to 60°C)
Relative Humidity	0% to 90% RH (Non-Condensing)
CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	RJ45 (MALE)
FEATURES & SPECIFICATIONS	
USB Specification	USB 1.1 (up to 12 Mbps)
Driver Required	No
Suspend Mode Support	Yes
STANDARDS & COMPLIANCE	
Certifications	RoHS, REACH, CE, FCC
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:  
<https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U009-015-RJ45-X](#)