

Heavy-Duty USB-A to USB Micro-B Cable - M/M, USB 2.0, UHMWPE and Aramid Fibers, Gray, 10 ft. (3.05 m)

MODEL NUMBER: **U050-010-GY-MAX**



Durable USB cable connects a smartphone or other Micro-B device to the USB-A port on your computer, wall charger or car charger.

Features

Heavily Reinforced Cable Charges and Syncs Your Smartphone or Other USB Micro-B Device This heavy-duty USB sync/charge cable (M/M) connects your smartphone, external hard drive, digital camera or other USB Micro-B device to a computer, car charger or wall charger. It allows you to charge and power your Micro-B device, as well as sync and transfer data at USB 2.0 speeds up to 480 Mbps. The cable is ideal for streaming audio and similar high-end applications that require fast, clear transmission free of line noise and other interference.

Constructed Using UHMWPE and Bulletproof Aramid Fiber Designed to Last Charging cables used with mobile devices are often pulled, strained and generally abused, sometimes to the point of failure. To counter the stress of daily abuse, the super-robust U050-010-GY-MAX is constructed using UHMWPE and Aramid fiber to reinforce the conductors inside the cable. The double-braided nylon jacket helps maintain top performance and long life, while the enhanced UHMWPE and Aramid protection stands up to the strain of rigorous and frequent use. Integral strain relief gives the cable extra flexibility, reduces stress, and helps the cable move freely without cracking or breaking loose from the connector.

Highlights

- Engineered using UHMWPE and Aramid fiber to stand up to frequent and rigorous use
- Extra-strong cable construction helps prevent fraying and loose cable connectors
- Supports USB 2.0 speeds up to 480 Mbps to ensure efficient charging and data transfers
- Integral strain relief helps cable move freely without stress or cracking
- Ideal for streaming video and other applications that require a fast, clear signal

Applications

- Charge and sync your smartphone or other Micro-B device from a USB computer or wall charger up to 10 ft. away
- Transfer data between an external hard drive or flash drive and your laptop or computer
- Replace a cable that became frayed or inoperable due to frequent use

System Requirements

- Device or charger with USB-A port
- Device with USB Micro-B port

Package Includes

- U050-010-GY-MAX Heavy-Duty USB-A to USB Micro-B Cable (M/M), Gray, 10 ft. (3 m)



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Specifications

OVERVIEW	
UPC Code	037332238962
Technology	USB 2.0 (High Speed); USB
PHYSICAL	
Color	Gray
Cable Outer Diameter (OD)	4.2mm
Cable Jacket Rating	VW-1
Cable Length (ft.)	10
Cable Length (m)	3
Cable Length (in.)	120
Material of Construction	PVC, UHMWPE, Aramid
Cable Length (cm)	304.8
Shipping Dimensions (hwd / in.)	0.50 x 7.00 x 10.00
Shipping Weight (kg)	0.10
Unit Packaging Type	Polybag
ENVIRONMENTAL	
Operating Temperature Range	-4 to 140 F (-20 to 60 C)
Storage Temperature Range	-4 to 176 F (-20 to 80 C)
Relative Humidity	0% to 90% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	MICRO-USB B (MALE)
Connector Plating	Nickel
Contact Plating	Gold
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
STANDARDS & COMPLIANCE	
Certifications	Tested to CE, RoHS, REACH
WARRANTY	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Product Warranty Period (Worldwide)	Lifetime limited warranty
--	---------------------------

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U050-010-GY-MAX](#)