

## 2-Port USB 2.0 Printer/Peripheral Sharing Switch

MODEL NUMBER: **U215-002**



Allows 2 computers to share one USB 2.0 peripheral, such as a printer, scanner or external hard drive, saving you money, space and time.

### Description

The U215-002 2-Port USB 2.0 Hi-Speed Printer/Peripheral Sharing Switch saves you money, time and precious workspace by letting you connect two computers to a single USB peripheral. Recommended for home and small offices, this sharing switch eliminates the cost of buying two printers, two scanners, two hard drives, etc., as well as the problem of where to put them and their cables.

One-touch port switching lets you switch between computers using a mouse, hotkeys or manual pushbutton. Idle time-out switching ensures all data is sent from the active printer buffer before switching ports.

A taskbar icon indicates the connected device's status. LEDs on the unit indicate which computer currently controls the device. The U215-002 is compatible with USB 2.0 and USB 1.1 devices and supports data transfer rates up to 480 Mbps.

No external power supply required. Switch is compatible with all USB-enabled Operating Systems. Optional CD software is compatible with Windows (XP and later) and Mac (OS X 10.3 and later).

NOTE: Customers are encouraged to use the 1.5 ft. USB cables provided between the source (e.g. PC) and switch. Using longer cables could cause an intermittent or connection loss.

### Features

#### Connect 2 Computers to a Single USB Device

- Recommended for printers, scanners, hard drives and other USB peripherals
- Saves money, time and workspace
- Ideal for home and small offices
- Compatible with USB 2.0 and USB 1.1 peripherals
- Supports data transfer rates up to 480 Mbps

#### One-Touch Port Switching

- Switch between computers with mouse, hotkey or manual pushbutton
- All data sent from active printer buffer before switching ports
- Taskbar icon indicates device status

### Highlights

- Switch between computers via mouse, hotkey or manual button
- Supports data transfer rates up to 480 Mbps
- Easy setup with included optional software CD
- No power adapter required

### System Requirements

- 1 or 2 computers with available USB ports
- Switch is compatible with all USB-enabled operating systems
- Optional software is compatible with Windows (XP and later) and Mac (OS X 10.3 and later)

### Package Includes

- U215-002 2-Port USB 2.0 Hi-Speed Printer/Peripheral Sharing Switch
- (2) USB 2.0 cables (A/B), 1.5 ft.
- Installation CD
- Owner's manual



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

- LEDs indicate computer control

#### Easy Setup and Broad Compatibility

- Switch is compatible with all USB-enabled Operating Systems
- Optional software is compatible with Windows (XP and later) and Mac (OS X 10.3 and later)
- No external power supply required

## Specifications

OVERVIEW	
UPC Code	037332198631
Technology	USB 2.0 (High Speed); USB
Host Connector	USB A (MALE)
INPUT	
Bus Powered	Yes
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Blue (1, 2)
PHYSICAL	
Color	Black
Material of Construction	ABS
Shipping Dimensions (hwd / cm)	3.81 x 11.18 x 9.50
Shipping Dimensions (hwd / in.)	1.50 x 4.40 x 3.74
Shipping Weight (kg)	0.12
Shipping Weight (lbs.)	0.26
Unit Dimensions (hwd / in.)	0.8 x 2.7 x 1.7
Unit Packaging Type	Box
Unit Weight (kg)	0.00
Unit Weight (lbs.)	0
ENVIRONMENTAL	
Operating Temperature Range	32 to 104 F (0 to 40 C)
Storage Temperature Range	14 to 131 F (-10 to 55 C)
Relative Humidity	5% to 90% RH, Non-Condensing
BTUs	1.7 BTU/Hr



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Power Consumption (Watts)	0.5
<b>CONNECTIONS</b>	
Ports	2
Side A - Connector 1	USB A (FEMALE)
Side B - Connector 1	(2) USB B (FEMALE)
Connector Plating	Nickel
<b>FEATURES &amp; SPECIFICATIONS</b>	
Port Selection	Pushbutton; Hotkey; Mouse
USB Specification	USB 2.0 (up to 480 Mbps)
Driver Required	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	Tested to CE, FCC, RoHS, REACH, WEEE
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U215-002](#)