

## Dual-Port USB Car Charger, Quick Charge - Dual USB-A 3.0, UL 2089 Certified

MODEL NUMBER: U280-C02-S-QC3U



Quick-charge USB car charger safely charges two mobile devices, including tablets and smartphones, in your vehicle at the same time.

### Features

**Quick-Charge USB Car Charger Charges 2 Mobile Devices in Your Vehicle Simultaneously** This dual USB car charger with Qualcomm Quick Charge 3.0 technology lets you quickly and safely charge two USB-powered mobile devices at the same time. You and a passenger can connect your smartphones, tablets or MP3 players, to name just a few compatible devices, to ensure satisfactory battery charge when you reach your destination. The dual-port USB car charger is certified to UL 2089 standards for vehicle battery adapters rated 24V DC or less.

**USB-C PD Charging Port Charges up to 4 Times Faster Than Conventional 5W Chargers** One of the two charging ports is powered by advanced Quick Charge 3.0 technology. Instead of charging at a preset power level, this charger adjusts to one of three possible power levels to provide as much power as your QC-compliant device's battery can handle. Available outputs include 3.6–6.5V 3A, 6.5–9V 2A and 9–12V 1.5A.

**Built-In Auto-Sensing Adjusts to Proper Power Level** The second USB port features auto-sensing technology that detects the connected device and automatically adjusts to the appropriate power level up to 5V 2.4A, perfect for fast-charging tablets and e-readers. It's compatible with Apple, Android, Windows and Amazon devices with USB-C, Thunderbolt 3 or USB-A charging ports.

**Works with the 12V DC Power Outlet in Your Vehicle** The compact dual USB car charger adapter connects to any standard 12V DC vehicle power outlet, such as the one on your dashboard. Just plug it in, and connect your devices' USB cables for fast, convenient mobile charging. An easy-to-see LED indicates the charger is receiving power.

### Highlights

- Dual USB car charger connects to the 12V DC power outlet in your car, truck or SUV
- Ideal for charging Apple, Android, Windows and Amazon devices while traveling
- Auto-sensing USB port adjusts charging power level to your device up to 5V 2.4A
- Achieves UL 2089 certification for vehicle battery adapters rated up to 24V DC

### Applications

- Charge a smartphone and a tablet or an Amazon Kindle Fire and a digital camera while driving to your destination
- Keep your Chromebook or MacBook constantly charged while on the road

### System Requirements

- Vehicle with standard 12V DC power outlet

### Package Includes

- U280-C02-S-QC3U USB Car Charger, Quick Charge

## Specifications

OVERVIEW	
UPC Code	037332218230
Product Type	Car Charger
Charging Form Factor	Direct Plug-In
Device Compatibility	Phone; Tablet; Amazon Kindle



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Technology	USB
<b>INPUT</b>	
Nominal Input Voltage(s) Supported	12V DC
Input Plug Type	Car Auxiliary Power Outlet
<b>OUTPUT</b>	
Output Capacity	30W
Overload Protection	Yes
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
LED Indicators	Blue (Power)
<b>CHARGING</b>	
Charging Ports / Amps	(1) 2.4A; (1) 3A / 2A / 1.5A
Number of Charging Ports	2
Total Charging Amps	3.5A
Charging Method	USB
Total Charging Watts	30
Charging Ports Detail	USB-A: 3.6V~6.5V/3A, 6.5V~9V/2A, 9V~12V/1.5A
Charging Port Type	(2) USB A (FEMALE)
Charging Method Detail	Quick Charge 3.0
<b>PHYSICAL</b>	
Color	White
Material of Construction	Polycarbonate, ABS UL94V-0
Shipping Dimensions (hwd / cm)	2.54 x 10.16 x 15.24
Shipping Dimensions (hwd / in.)	1.00 x 4.00 x 6.00
Shipping Weight (kg)	0.03
Shipping Weight (lbs.)	0.07
Unit Dimensions (hwd / cm)	3.75 x 7.05 x 2.55
Unit Dimensions (hwd / in.)	1.48 x 2.78 x 1.00
Unit Packaging Type	Polybag
Unit Weight (kg)	0.03
Unit Weight (lbs.)	0.06
<b>ENVIRONMENTAL</b>	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Operating Temperature Range	32 to 104 F (0 to 40 C)
Storage Temperature Range	-4 to 140 F (-20 to 60 C)
Power Consumption (Watts)	30
Operating Humidity Range	30 TO 90% RH, Non-Condensing
Storage Humidity Range	10 TO 90% RH, Non-Condensing
<b>CONNECTIONS</b>	
Ports	2
Side A - Connector 1	Car Cigarette Lighter
Side B - Connector 1	(2) USB A (FEMALE)
<b>FEATURES &amp; SPECIFICATIONS</b>	
Driver Required	No
Quick Charge Compliant	3.0
<b>SPECIAL FEATURES</b>	
Overcurrent Protection	Yes
Overvoltage Protection	Yes
GaN Technology	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	Tested to CE, FCC, RoHS, REACH, QC 3.0 Quick Charge, UL 2089 3rd Edition
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U280-C02-S-QC3U](#)