

USB 3.0 SuperSpeed Adapter - USB-A to USB-A, M/F, Up Angle, Black

MODEL NUMBER: U324-000-UP



- Converts a standard USB port into a more convenient up-angled USB port in tight spaces, such as behind furniture or against a wall.

Features

One-Piece Adapter Connects Computers, Printers, Modems and Other USB Equipment This palm-sized USB adapter connects your computer, laptop or other compatible USB-A device, such as a Chromebook or Surface Pro tablet, to a USB-A keyboard, printer, portable hard drive, flash drive, patch panel or other peripheral. It supports USB 3.0 data transfer speeds up to 5 Gbps, which is 10 times faster than USB 2.0. The fully molded piece is small enough to carry in your pocket, purse or laptop bag.

Up-Angle USB-A Port Makes Connecting and Disconnecting Easier in Tight Spaces The female USB connector is designed at a 90-degree up angle, which makes it easier to reach in from above to connect cables where space is at a premium. This helps you, for instance, save space in your workspace by letting you push your PC flush against the wall or the back of a cabinet. Instead of leaving space in the rear for protruding USB cables, the U324-000-UP allows you to connect cables parallel to your computer.

Highlights

- Recommended for powering computers, printers and other home/office peripherals
- 90-degree-angled form factor is ideal for tight spaces, such as flush against a wall
- Supports USB 3.0 SuperSpeed data transfer rates up to 5 Gbps—10x faster than USB 2.0
- Durable one-piece molded adapter fits easily in pocket or bag for connecting anywhere
- Plug-and-play operation with no software required for easy, immediate installation

Applications

- Connect devices like computers, servers and external hard drives in your data center, workspace or home theater
- Create a USB connection in a hard-to-reach space, such as against a wall or behind a desk

Package Includes

- U324-000-UP USB 3.0 SuperSpeed Adapter

Specifications

OVERVIEW	
UPC Code	037332248671
Technology	USB 3.0 (SuperSpeed)
PHYSICAL	
Color	Black



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Material of Construction	PVC
Shipping Dimensions (hwd / in.)	5.00 x 4.00 x 0.50
Unit Packaging Type	Polybag
ENVIRONMENTAL	
Operating Temperature Range	32 to 122 F (0 to 50 C)
Storage Temperature Range	-4 to 140 F (-20 to 60 C)
Relative Humidity	10 - 90%, Non-Condensing
CONNECTIONS	
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	USB 3.0 A (FEMALE)
Connector Plating	Nickel
Contact Plating	Gold
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.0 (up to 5 Gbps)
STANDARDS & COMPLIANCE	
Certifications	Tested to RoHS and REACH
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U324-000-DN](#) [U324-000-UP](#)