

## USB-C Female to USB-A Male Adapter, USB 3.0

MODEL NUMBER: U329-000



USB-A male to USB-C female adapter connects your smartphone, tablet or Ultrabook to a laptop or desktop PC.

### Features

**Use Your Existing USB-A Device with a USB Type-C Cable** Recommended for charging or synchronizing data on your USB-A computer, laptop or tablet Data transfer speeds up to 5 Gbps—10 times faster than USB 2.0 Backward compatible with previous USB generations

**Reversible USB-C Female Connector** Fumble-free reversible port can be connected in either direction to ensure fast, easy connection every time

**Premium Construction** Molded connectors and gold-plated contacts for maximum conductivity and minimum data loss Slim, sleek design tailored for emerging design trends toward smaller devices

### Highlights

- Data transfer speeds up to 5 Gbps—10 times faster than USB 2.0
- Supports power output up to 900mA
- Reversible USB-C port provides fumble-free connection
- Gold-plated contacts for maximum conductivity and minimum data loss
- Backward compatible with previous USB generations

### System Requirements

- USB-A host
- Device with USB-C female connector
- USB Type-C M/M Cable

### Package Includes

- U329-000 USB 3.0 SuperSpeed Adapter, USB-A Male to USB Type-C Female (M/F)

## Specifications

| OVERVIEW                                 |                           |
|--|---------------------------|
| UPC Code                                 | 037332213976              |
| Technology                               | USB; USB 3.0 (SuperSpeed) |
| INPUT                                    |                           |
| Bus Powered                              | Yes                       |
| POWER                                    |                           |
| USB Power Delivery (PD) Charging Support | No                        |
| USER INTERFACE, ALERTS & CONTROLS        |                           |



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

|                                       |  |
|---------------------------------------|--|
| LED Indicators                        | N/A  |
| <b>PHYSICAL</b>                       |  |
| Color                                 | Black  |
| Material of Construction              | PVC, UL94V-0   |
| Shipping Dimensions (hwd / cm)        | 14.99 x 9.91 x 1.27                                  |
| Shipping Dimensions (hwd / in.)       | 5.90 x 3.90 x 0.50                                   |
| Shipping Weight (lbs.)                | 0.02   |
| Unit Dimensions (hwd / cm)            | 0.79 x 1.6 x 2.79                                    |
| Unit Dimensions (hwd / in.)           | 0.31 x 0.63 x 1.10                                   |
| Unit Packaging Type                   | Polybag  |
| Unit Weight (kg)                      | 0.00   |
| Unit Weight (lbs.)                    | 0.01   |
| <b>ENVIRONMENTAL</b>                  |  |
| Operating Temperature Range           | 32 to 113 F (0 to 45 C)                              |
| Storage Temperature Range             | 14 to 158 F (-10 to 70 C)                            |
| Operating Humidity Range              | 10% to 85% RH, Non-Condensing                        |
| Storage Humidity Range                | 5% to 90% RH, Non-Condensing                         |
| Power Provided to Connected Device(s) | 5V, 0.9A   |
| <b>CONNECTIONS</b>                    |  |
| Ports                                 | 1  |
| Side A - Connector 1                  | USB A (MALE)   |
| Side B - Connector 1                  | USB C (FEMALE)                                       |
| Connector Plating                     | Nickel   |
| Contact Plating                       | Gold   |
| <b>FEATURES &amp; SPECIFICATIONS</b>  |  |
| USB Specification                     | USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps) |
| Driver Required                       | No   |
| <b>STANDARDS &amp; COMPLIANCE</b>     |  |
| Certifications                        | Tested to CE, FCC, RoHS, REACH                       |
| <b>WARRANTY</b>                       |  |
| Product Warranty Period (Worldwide)   | 3-year limited warranty                              |



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:  
<https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U329-000](#)