


Tripp Lite's USB 3.0 Fiber Transceivers only work in conjunction with network switches.

USB 3.0 Singlemode Fiber Optic Transceiver Ethernet Adapter, 10/100/1000 Mbps, 1310nm, 5km, LC

MODEL NUMBER: U336-SMF-1G-LC



Connects your USB-enabled computer or laptop to a 10/100/1000 Mbps fiber optic network without installing an internal Ethernet card.

Features

Connects Your USB Device to a Wired Ethernet Network without an Internet Card Installed This USB to LC fiber optic Ethernet adapter allows you to instantly connect your computer, laptop, tablet or other USB-compatible device to a wired 10/100/1000 Mbps fiber optic network, even if your device has no NIC (Network Interface Controller) installed. The adapter offers access to a Gigabit Ethernet network when Wi-Fi is unavailable or when a wired connection offers faster speeds. It transmits data up to 5 kilometers (3.1 miles) from your fiber network using a wavelength of 1310nm.

Hot-Swappable for Installation Without Network Interruption This USB 3.0 LC Fiber Transceiver Ethernet adapter is fully hot-swappable, so you can install it without a potentially costly network shutdown or device reboot. Just connect the built-in USB cable to your device's USB port (which also powers the adapter), and connect the LC duplex port to a high-speed network switch, router or hub using existing or newly run singlemode fiber cable (such as Tripp Lite's N370-Series, sold separately).

Delivers Full Gigabit Ethernet Performance with Audio and Video Streaming The compact USB to Ethernet adapter supports full 1 Gbps network speeds and USB 3.0 speeds, allowing you to transfer data efficiently and stream audio and video. The direct fiber connection minimizes the risk of data leaks and electromagnetic interference (EMI). A blue LED indicates successful Ethernet connection and data transfer. The adapter works with Windows and Microsoft Server operating systems.

Highlights

- Connects you to a wired Gigabit Ethernet network when Wi-Fi is weak or unavailable
- Provides 1 Gbps throughput up to 5 kilometers (3.1 miles) via singlemode fiber cabling
- Supports USB 3.0 speeds up to 5 Gbps to ensure efficient data transfers
- Hot-swappable interface lets you install and uninstall without shutting down computer
- USB 3.0 Fiber Transceiver Ethernet adapter powered via USB, so no external power supply is required
- Works with most laptops and PC running Windows and Microsoft Servers.

Applications

- Install an LC duplex port on your Chromebook or PC for the purpose of connecting a singlemode Gigabit Ethernet network cable
- Upload data from your notebook or download data from the Ethernet at true 10/100 Mbps speeds
- Replace a malfunctioning Ethernet card on your laptop or computer

System Requirements

- Computer or laptop with USB-A port (USB 3.0 is required to attain USB 3.0 speeds)



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- Windows (through Win 10),
Server (2012 or 2008)
- Network switch

Package Includes

- U336-SMF-1G-LC USB 3.0
Ethernet NIC Adapter
- Driver CD
- Quick Start Guide

Specifications

OVERVIEW	
UPC Code	037332225986
Technology	USB; USB 3.0 (SuperSpeed); USB 3.1 (Gen 1)
Mode Type	Singlemode
INPUT	
Built-In Cable Length (m)	0.155
Built-In Cable Length (in.)	6.1
Bus Powered	Yes
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Blue (Power/Data)
PHYSICAL	
Color	White
Cable Jacket Rating	VW-1
Material of Construction	ABS, PVC
Unit Dimensions (hwd / in.)	0.71 x 2.2 x 1.61
Unit Packaging Type	Box
Unit Weight (kg)	0.05
Unit Weight (lbs.)	0.12
ENVIRONMENTAL	
Operating Temperature Range	32 to 131°F (0 to 55°C)
Storage Temperature Range	32 to 140°F (0 to 60°C)



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Relative Humidity	5% to 90 % RH, Non-Condensing
COMMUNICATIONS	
Network Speed	1Gbps
Wavelength	1310nm
Transmission Distance	5km
CONNECTIONS	
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	LC DUPLEX (FEMALE)
Connector Plating	Nickel
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	Yes
Remote Wakeup Support	Yes
Optical Port	LC
STANDARDS & COMPLIANCE	
Certifications	CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U336-SMF-1G-LC](#)