

USB-C to Gigabit Network Adapter with Right Angle USB-C, Thunderbolt 3 Compatibility - White

MODEL NUMBER: U436-06N-GBW-RA



Connects the USB-C or Thunderbolt 3 port on your computer, laptop, MacBook, Chromebook or tablet to a wired Gigabit Ethernet network.

Features

USB-C to Gigabit Ethernet Adapter Connects to Your Laptop's USB-C or Thunderbolt 3 Port This USB Type-C to Gigabit Ethernet NIC Network Adapter (M/F) allows your computer, tablet, laptop, notebook, MacBook, Chromebook, Ultrabook or smartphone to connect to a wired Ethernet network. Connect the right-angle USB-C connector to your device's USB-C or Thunderbolt 3 port, and connect the RJ45 port to a UTP cable (such as Tripp Lite's N201-Series, sold separately). Ideal for settings in which no Wi-Fi is available or when a wired connection offers faster speeds, this USB 3.1 Gen 1 adapter lets you enjoy true 10/100/1000 Mbps Ethernet speeds for fast data transfers and audio/video streaming.

Built-In USB-C Cable Attaches in Either Direction Unlike traditional USB cables that connect in only one direction, the reversible USB-C male connector plugs into a USB-C or Thunderbolt 3 port in either direction for a fumble-free connection every time.

Right-Angle USB-C Plug Makes Connecting in Tight Spaces Easier The space-saving right-angle USB-C plug is easy to install in confined spaces, such as behind your computer desk or workstation. The right-angle construction also relieves strain on the cable and connector and prevents the cable from bending awkwardly.

Ready to Use Right Out of the Package The plug-and-play network adapter requires no software, drivers or external power. The compact unit fits easily into a pocket, briefcase or laptop bag for connecting on the go. Plug it into your laptop for instant network connection.

Highlights

- Connect to a wired 10/100/1000 Mbps network where Wi-Fi is weak or unavailable
- More convenient, less expensive than installing or upgrading an internal Ethernet card
- Widely compatible with Windows, Mac and Chromium operating systems
- Right-angle USB-C plug allows easier connection in confined or hard-to-reach spaces
- Plug-and-play operation with no software required for easy, immediate installation

Applications

- Access a wired Ethernet network in a location with no or spotty Wi-Fi
- Upload data from your MacBook or download data from the Ethernet at true 10/100/1000 Mbps speeds

System Requirements

- Laptop or computer with an available USB-C port
- Ethernet network and a Cat6 cable to connect to it.

Package Includes

- U436-06N-GBW-RA Right-Angle USB-C to Gigabit Ethernet Network Adapter (M/F), White
- Quick Start Guide



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Specifications

OVERVIEW	
UPC Code	037332214157
Technology	USB 3.1 (Gen 1)
INPUT	
Built-In Cable Length (ft.)	0.328
Built-In Cable Length (m)	0.1
Built-In Cable Length (in.)	3.94
Bus Powered	Yes
Product Length (in.)	6
Product Length (cm.)	15.24
Product Length (ft.)	0.5
Product Length (m.)	0.15
BATTERY	
Battery Charging (5V/1.5A Port)	No
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Network cable connected = Green; Data transmitting = Green
PHYSICAL	
Color	White
Cable Jacket Rating	VW-1
Material of Construction	ABS, PVC
Unit Dimensions (hwd / in.)	0.63 x 6 x 1.06
Unit Dimensions (hwd / mm)	16 x 150 x 27
Unit Packaging Type	Box
ENVIRONMENTAL	
Operating Temperature Range	32 to 113° F (0 to 45° C)
Storage Temperature Range	14 to 176° F (-10 to 70° C)
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non-Condensing



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

COMMUNICATIONS	
Network Speed	1Gbps
CONNECTIONS	
Ports	1
Side A - Connector 1	USB C (MALE) - RIGHT ANGLE
Side B - Connector 1	RJ45 (FEMALE)
Connector Plating	Nickel
Contact Plating	Gold
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No
Recommended Category Cable	Cat6
STANDARDS & COMPLIANCE	
Certifications	CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U436-06N-GBW-RA](#)