

Portable Charger - 2x USB-A, 10,400mAh Power Bank, Lithium-Ion, Auto Sensing, Black

MODEL NUMBER: UPB-10K4-S2U



Compact 2-port 10,400mAh power bank charges multiple smartphones, tablets, e-readers, MP3 players and other handheld mobile devices anywhere, anytime, without plugging into an AC power outlet.

Features

Travel-Sized for Convenient Charging of Dual Devices Anywhere

- Compact form fits comfortably in your purse or backpack
- Ideal for charging up to 2 smartphones, tablets, e-readers, MP3 players and other handheld mobile devices simultaneously
- Works with Android, Apple and Windows devices

Built-In 10,400mAh Lithium-Ion Battery Charges Without an AC Power Outlet

- Charges at maximum power draw for hours to ensure your devices are ready when you need them
- Dual USB ports provide up to 5V 1A and 5V 2.4A of power
- Auto-sensing 2.4A port adjusts amperage to match amperage of connected device
- Protects against short circuits, overvoltage, overcurrent, overcharges and overdischarges

Easy to Recharge for the Next Time You Leave Home or Office

- USB Micro-B port connects to USB charger or computer's USB-A port to charge internal battery
- Built-in LEDs indicate at a glance how much battery capacity is left
- 3 ft. USB Micro-B charging cable included

Highlights

- Dual USB-A ports provide up to 5V 1A and 5V 2.4A of power
- Auto-sensing port adjusts amperage to match connected device
- LEDs indicate remaining battery capacity at a glance
- 3-ft. (0.91 m) USB Micro-B charging cable included
- Compact form fits comfortably in your purse or backpack

Package Includes

- UPB-10K4-S2U 10,400mAh Dual-Port Mobile Power Bank USB Battery Charger
- USB Micro-B cable, 3 ft.
- Owner's manual

Specifications

OVERVIEW



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

UPC Code	037332203922
Product Type	Portable Charger
Charging Form Factor	Portable
Device Compatibility	Phone; Tablet; Amazon Kindle
Over Current Protection	Yes
Technology	USB
INPUT	
Nominal Input Voltage(s) Supported	5V DC
Input Plug Type	USB MICRO-B (FEMALE)
Input Plug Type Detail	USB-A to USB Micro B cable provided
OUTPUT	
Overload Protection	Yes
CHARGING	
Charging Ports / Amps	(1) 1A; (1) 2.4A
Number of Charging Ports	2
Total Charging Amps	2.4A
Charging Method	USB
Total Charging Watts	12
Charging Ports Detail	USB-A: 5V/1A or 5V/2A
Charging Port Type	(2) USB A (FEMALE)
Charging Method Detail	10,400 mAh
PHYSICAL	
Color	Black
Material of Construction	ABS
Shipping Dimensions (hwd / cm)	4.60 x 23.50 x 11.81
Shipping Dimensions (hwd / in.)	1.81 x 9.25 x 4.65
Shipping Weight (kg)	0.45
Shipping Weight (lbs.)	0.99
Unit Dimensions (hwd / cm)	14 x 6.4 x 2.5
Unit Dimensions (hwd / in.)	5.5 x 2.5 x 1
Unit Weight (kg)	0.27
Unit Weight (lbs.)	0.6



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

ENVIRONMENTAL	
Operating Temperature Range	32 to 113 F (0 to 45 C)
Storage Temperature Range	5 to 113 F (-15 to 45 C)
Relative Humidity	0% to 90% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	MICRO-USB B (FEMALE)
Side B - Connector 1	(2) USB A (FEMALE)
Connector Plating	Nickel
Contact Plating	Nickel
SPECIAL FEATURES	
Overcurrent Protection	Yes
Overvoltage Protection	Yes
GaN Technology	No
STANDARDS & COMPLIANCE	
Certifications	Tested to CE, FCC, RoHS
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[UPB-10K4-S2U](#)