



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

## 900VA 480W Line-Interactive UPS with 6 Outlets - AVR, VS Series, 120V, 50/60 Hz, Tower

MODEL NUMBER: VS900T



Line-interactive UPS provides basic battery backup with AVR protection for your office computer, home theater setup or digital signage.

### Features

**900VA/480W/120V Battery Backup for PCs, Home Theater or Digital Signage** This 120V UPS with AVR protection provides reliable battery backup and AC power protection against blackouts, brownouts, surges and line noise that can damage valuable electronics or destroy data. The six-outlet 120V battery backup is ideal protection for your home office, media center or commerce components, including computers, routers, printers, HDTVs, Blu-ray players, game consoles, ATMs, security systems and digital signage equipment.

**Allows Time to Back Up Critical Files During a Blackout** Backup support allows you to work through short power failures, and gives you enough time to safely save files and shut down your system in case of a prolonged blackout. Backup time varies according to load, but the line-interactive UPS system should keep an energy-efficient desktop computer with small LCD monitor powered as long as 44 minutes. During normal operation, incoming utility power keeps the replaceable internal battery fully charged, so backup power will always be available.

**Connects Your Equipment to 6 NEMA 5-15R Outlets** Four 5-15R outlets provide both battery backup and surge protection for your computer, monitor and other crucial components. The other two 5-15R outlets are surge-protected only for printers, scanners and other non-essential equipment. A high 95% line mode efficiency rating reduces BTU emissions, energy consumption and, ultimately, your energy costs.

**Automatic Voltage Regulation (AVR) Corrects Low-Voltage Conditions** AVR protects your equipment from incremental hardware damage, data loss and performance problems caused by brownouts. The VS900T can correct brownouts as low as 89V and overvoltages as high as 145V back to nominal 120V power without drawing on the battery backup needed to support your equipment during a blackout.

**316 Joules Fight Back Against Unexpected Power Surges** A 316-joule surge suppression rating protects connected components from the harmful effects of power surges.

**Combats Electromagnetic Interference That Can Harm Equipment** Various electromagnetic and radio sources found in virtually every home and business can cause disruptive interference on the AC line. Known as EMI (electromagnetic interference) and RFI (radio frequency interference), this line noise is a common cause of performance problems and can lead to incremental hardware damage, data corruption and audio/video transmission problems. The VS900T incorporates technology that filters out disruptive line noise so that it won't affect your equipment.

**Easy-to-Read LEDs Report Real-Time UPS and Power Status** Three front-panel LED indicators monitor essential information, such as online, battery and fault modes. An audible alarm will sound in case of low battery, excessive load and fault condition.

**Tower Form Factor for Easy Placement in Your Workspace or Media Center** The long-lasting ABS housing fits easily on a desktop, shelf or anywhere else convenient to your workstation or home theater. The five-foot power cord with NEMA 5-15P plug connects to a properly grounded AC wall outlet.

### Highlights

- Protects valuable equipment from dangers posed by brownouts, surges and line noise
- AVR battery backup allows time to save files and safely shut down during blackouts
- 6 NEMA 5-15R outlets provide power to PC, home theater or digital signage equipment
- Alarm and front-panel LEDs report online, battery, fault and overload conditions
- High 95% efficiency with low BTU ratings saves power and lowers your energy costs

### Applications

- Protect your PC and other sensitive electronics against power surges, brownouts and blackouts
- Operate essential equipment during short-term power outages using battery backup power
- Shut down PCs, DVRs, routers and other equipment without data loss during long-term power outages

### Package Includes

- VS900T 900VA 480W Line-Interactive UPS with 6 Outlets
- Owner's manual



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

## Specifications

OVERVIEW	
UPC Code	037332212900
UPS Type	Line-Interactive
INPUT	
Rated input current (Maximum Load)	10A
Nominal Input Voltage(s) Supported	120V AC
UPS Input Connection Type	5-15P
Input Circuit Breakers	10A input breaker
UPS Input Cord Length (ft.)	5
UPS Input Cord Length (m)	1.5
Recommended Electrical Service	15A 120V
Input Phase	Single-Phase
OUTPUT	
Output Volt Amp Capacity (VA)	900
Output Watt Capacity (Watts)	480
Nominal Voltage Details	120v nominal output in battery mode
Frequency Compatibility	60 Hz
Output Voltage Regulation (Line Mode)	120V (+9%, -12%)
Output Voltage Regulation (Battery Mode)	120V (+/- 10%)
UPS Output Receptacles (Surge Suppression Only)	4 UPS outlets, 2 surge-only outlets
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	PWM sine wave
Nominal Output Voltage(s) Supported	110V; 115V; 120V
Output Receptacles	(6) 5-15R
Individually Controllable Load Banks	No
BATTERY	
Battery Type	Valve Regulated Lead Acid (VRLA)
Half Load Runtime (min.)	3.8 min. (240w)



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Expandable Runtime	No
DC System Voltage (VDC)	12
Battery Recharge Rate (Included Batteries)	8 hours (10% to 90%)
<b>VOLTAGE REGULATION</b>	
Voltage Regulation Description	Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 89 to 145
Overvoltage Correction	Input voltages between 132 and 145 are reduced by 15%
Undervoltage Correction	Input voltages between 89 and 108 are boosted by 18%
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Switches	Controls off/on power status
Audible Alarm	Audible alarm indicates low-battery, fault, overload and replace-battery status
LED Indicators	3 LEDs indicate online mode (green), battery mode (yellow) and fault mode (red)
<b>SURGE / NOISE SUPPRESSION</b>	
UPS AC Suppression Joule Rating	316
UPS AC Suppression Response Time	Instantaneous
UPS Dataline Suppression	N/A
EMI / RFI AC Noise Suppression	Yes
<b>PHYSICAL</b>	
Installation Form Factors Supported with Included Accessories	Tower
Primary Form Factor	Tower
Primary UPS Depth (mm)	300
Primary UPS Height (mm)	142
Primary UPS Width (mm)	102
Shipping Dimensions (hwd / in.)	8.60 x 5.30 x 13.70
Shipping Weight (kg)	6.24
UPS Housing Material	ABS
UPS Power Module Dimensions (hwd, in.)	5.6 x 4 x 11.8
UPS Power Module Weight (kg)	5.72
UPS Power Module Weight (lbs.)	12.6
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Storage Temperature Range	+5 to +113 degrees Fahrenheit / -15 to +45 degrees Celsius
Relative Humidity	0 to 90%, non-condensing
AC Mode BTU / Hr. (Full Load)	66
AC Mode Efficiency Rating (100% Load)	95%
<b>COMMUNICATIONS</b>	
Network UPS Tools Compatibility	
Communications Interface	None
<b>LINE / BATTERY TRANSFER</b>	
Transfer Time	6 milliseconds
Low Voltage Transfer to Battery Power (Setpoint)	89
High Voltage Transfer to Battery Power (Setpoint)	145
<b>SPECIAL FEATURES</b>	
High Availability UPS Features	Automatic Voltage Regulation (AVR); Surge/noise protection
<b>STANDARDS &amp; COMPLIANCE</b>	
UPS Certifications	Meets FCC Part 15 Category A (EMI); Tested to CSA (Canada); Tested to NOM (Mexico); Tested to UL1778 (USA)
Certification Details	UL1778: 2014 5th EDITION; CAN/CSA-C22.2 NO. 107.3:2014 3rd EDITION;
<b>WARRANTY</b>	
Product Warranty Period (U.S. & Canada)	3-year limited warranty
Product Warranty Period (Latin America)	3-year limited warranty
Product Warranty Period (International)	2-year limited warranty
Product Warranty Period (Mexico)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[VS900T](#)