# **Open Type Trimmer**

# Model 37



#### Features:

- 9 mm single turn
- Open frame
- Cermet
- RoHS compliant



# **Model Styles Available**

Top Adjust (with extension)	37F
Top Adjust	37P
Side Adjust	37W
Side Adjust (with extension)	37S

### **Electrical**

Resistance Range	100 to 1,000,000 Ohms
Standard Resistance Tolerance	± 20%
Input Voltage, Maximum	250 V
Power rating, Watts	0.5 @ 70°C
End Resistance, Maximum	<500 ohms: 10 Ohms Max; > 500 ohms: 2% Max.
Actual Electrical Travel	280° ±15°
Insulation Resistance, Minimum	100 Megohms
Resolution	Essentially infinite
Contact Resistance Variation	5% Max.
Temperature Coefficient of Resistance	±250 ppm/°C

## Mechanical

Torque, Maximum	4.5 in. oz.
Weight, Approx.	0.01 oz.
Wiper Position	Approx. 50%


# **Open Type Trimmer**

# Model 37



Environmental		
Operating Temperature Range	-30°C to +100°C	
Rotational Life, 50 Cycles	±10% ΔR	
Load Life, 0.5W, 500 Hours, 70°C	±5% ΔR	
Resistance to Solder Heat	260°C for 3 sec.	
Aqueous cleaning not recommended		

# **Ordering Information**



# **Circuit Diagram**

## **Standard Resistance Values, Ohms**

Resistance (ohms)	Part Marking
100	101
200	201
500	501
1K	102
2K	202
5K	502
10K	103
20K	203
50K	503
100K	104
200K	204
500K	504
1MEG	105


# **Open Type Trimmer**

# Model 37




# **Outline Drawings**


### Model 37F (Top Adjust with extension)




#### Model 37P (Top Adjust)



### Model 37W (Side Adjust)



### Model 37S (Side Adjust with extension)



# **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

### TT Electronics:

37PR1KLF 37PR10KLF 37WR1KLF 37WR10KLF 37WR2KLF 37FR1MEGLF 37SR1MEGLF 37WR1MEGLF
37PR1MEGLF 37FR2KLF 37PR20KLF 37SR20KLF 37WR20KLF 37WR200LF 37PR2KLF 37FR100LF
37SR500LF 37PR500LF 37PR200KLF 37PR500KLF 37SR200LF 37WR200LF 37FR10KLF 37WR500KLF
37SR500KLF 37PR200LF 37FR5KLF 37FR500KLF 37FR200KLF 37PR5KLF 37SR200KLF 37WR200KLF
37SR2KLF 37SR100LF 37PR100LF 37FR50KLF 37SR1KLF 37WR100LF 37FR200LF 37FR20KLF 37WR5KLF
37FR1KLF 37PR100KLF 37SR10KLF 37SR10KLF 37SR10KLF 37PR50KLF 37WR50KLF 37WR100KLF 37FR100KLF 37FR50KLF 37SR5KLF