


612W MEDICAL OPEN FRAME STANDBY & REMOTE ON/OFF

T7364AT



Features:

- EC/EN/ANSI/AAMI ES60601-1 (Edition 3.1)
- Means of Protection : 2 X MOPP
- Touch Current : < 100µA
- Meet IEC/UL 60950-1
- 100-240VAC Universal Input

Description:

Our Open Frame Medical range of 612 watt Power supplies have MOPP protection and are up to 95% efficient with full universal input, available with 12-48vdc single output, Remote Control On/Off and come with a 2 year standard warranty.

Specification	
Part Number	T7364AT
Rated Input Voltage	100-240V
O/P Voltage	24V
O/P Current	25A
Standby	5V / 1A
O/P For Fan	12V / 0.6A
Watt	612W
Line Frequency	50-60Hz
Current	7.0A - 2.7A
Protection	Internal Primary Circuit Fuse
Load Regulation	±5%
Ripple & Noise	1% Vp-p Max. For Output Voltage At Full Load
Transient Response	0.5mS for 50% Load Change Typical
Hold-up Time	10mS At Full Load
Protection	Short Circuit Protection /Over Voltage Protection / Over Current Protection / Over Temperature Protection
Safety	CB / UL / CUL / FCC / CE
MTBF	300,000 Calculated Hours at 25oC , by Telcordia SR-332
Operating Temperature	-20 to +50°C
Storage Temperature	-20 to +80°C
Operating Humidity	20 to 80% RH
Storage Humidity	10 to 90% RH
Cooling	Natural Convection Cooling
Dimensions	L 203.2 × W 127 × H 40 (mm)
Weight	1100g

General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

TT Electronics | Stontronics Ltd
Chancerygate Business Centre, Cradock Road, Reading RG2 0AH, UK
t: +44 (0) 118 931 1199

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TT Electronics:](#)

[T7364AT](#)