

63.50
[2,500]
TYP

55.58
[2,188]
TYP

12.70
[.500]
TYP

20.50
[.807]
TYP



29.74
[1,171]



73.02
[2,875]
TYP

Ø3.63
[.143]
4 PLC

R4.37
[.172]
4 PLC

RECOMMENDED PANEL CUT-OUT
SCALE 2:1

	201532-4
	201532-2
MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN 28 JUN 96 C. REIFSNYDER CHK 13 MAR 96 R. STONE APPROVED 25 JUN 96 G. STEINHAUER		 Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.38[.015] 3 PLC ± - 4 PLC ± - ANGLES ± -		NAME RECEPTACLE HOUSING, 104 POSITION, M SERIES	
		PRODUCT SPEC — APPLICATION SPEC —		SIZE CAGE CODE DRAWING NO	
MATERIAL SEE CALLOUTS		FINISH —		WEIGHT —	
		CUSTOMER DRAWING		SCALE 4:1 SHEET 1 of 1 REV V	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[201532-1](#)