







- ⚠ PLUG ACCEPTS JACKS MEETING DIN 72594-1,
ROAD VEHICLES - RADIO FREQUENCY INTERFACE - DIMENSIONS AND ELECTRICAL REQUIREMENTS.
2. PLUG SUBASSEMBLY WILL ACCEPT RG-316, RG-174 OR RG-174 LOW LOSS COAXIAL CABLE.
3. CRIMP FERRULE USING MIL HAND TOOL M22520/5-01 WITH DANIELS DIE SET Y1637 (.128 INCH HEX)
OR AMP PROCRIMPER II WITH DIE SET 58483-1 PER TYCO ELECTRONICS SPECIFICATION 408-8428.
4. SOCKET CONTACT 1438896-4 MUST BE PURCHASED SEPERATELY.
5. SUBASSY 1924937-1 (EXTENDED DIELECTRIC) IS ALLOWED AS AN ALTERNATE TO
SUBASSY 1924791-1.

REVISIONS					
P.	LTR	DESCRIPTION	DATE	DWN	APVD
B2		ECO-13-012147	29AUG2013	KP	LV
B3		REVISED PER ECO-16-008496	07JUN2016	DD	LV
B4		REVISED PER ECO-19-002003	07FEB2019	CN	AP






DETAIL D



DETAIL H



DETAIL Z

4805 (3/13)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2035141-2](#)