

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

—

© COPYRIGHT

By

ALL RIGHTS RESERVED

LOC
DF

DIST
DO

REVISIONS

DESCRIPTION

DATE _____

	DWN
--	-----

APV


[illegible]

DD-250 (REV. 5-22-64) 14 005070

	1.0 MAC
--	---------

	RIK
--	-----

484



1. THIS RCPT. IS DESIGNED TO CONFORM TO THE LATEST ISSUE OF MIL-C-24308. EXCEPT AS NOTED HEREIN.
2. MAX WIRE INSUL TO BE USED WITH THIS RCPT IS .054 DIA
3. METAL RETENTION CLIPS ARE INCLUDED IN INSERTS
4. THIS RCPT. WILL ACCEPT SIZE 22 SOCKET CONTACT M 39029/57-354 OR ANY AMP HDD-22 SOCKET CONTACT



5 UL & CSA DESIGNATION STAMPED ON SHELL,OPTIONAL

⑥ Diallyl Phthalate per MIL-M-14, Type SDG-F
Color: Blue
OR Polyphenylene Sulfide (PPS)
per MIL-M24519, Type GST-40F
Color: Black


7 STEEL PER ASTM-A-109 OR EQUIVALENT.

△ 8 CADIUM PER QQ-P-416, TYPE II, CLASS 2
OVER COPPER PER MIL-C-14550, CLASS 4.



MILITARY PART NUMBER MARKED (NEAR SIDE) —
MFG'S NAME, BRAND OR LOGO, MFG'S PART NUMBER
AND DATE CODE MARKED (FAR SIDE)



SOCKET CONTACT
 PART NO 204351-1
 QTY 44
 SUPPLIED WITH CONNECTOR
 BUT NOT INSTALLED



INSERTION/EXTRACTION TOOL
PART NO 91067-1
SUPPLIED WITH CONNECTOR
(-3 ONLY)

				M24308/2-19F	M24308/2-19F	204516-3
-				M24308/2-13F	M24308/2-13F	204516-2
REMARKS	INSERT MATERIAL	SHELL MATERIAL	SHELL FINISH	MILITARY PART NO ON PACKAGE	MILITARY PART NO ON PACKAGE	PART NO.
THIS DRAWING IS A CONTROLLED DOCUMENT.				OWN J. A. BAKER CHK - APVD -	 TE Connectivity	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		
		0 PLC ± -		PRODUCT SPEC		
		1 PLC ± -		-		
		2 PLC ± -		APPLICATION SPEC		
		3 PLC ± .005		-		
		4 PLC ± ± -		SIZE CAGE CODE DRAWING NO RESTRICTED		
MATERIAL SEE TABLE		FINISH SEE CALLOUTS		WEIGHT -		
CUSTOMER DRAWING				A1 00779		
				SCALE 4:1		SHEET 1 OF 1 REV H

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[M24308/2-13F](#)