




LOC —	DIST —	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			Y	REV PER ECO 15-016064	11-9-15	CT	CD



AMP P/N 206071-1
GSFC P/N G-08-S1

	.120 [3.05]	CI-2A-019-004V-001	1-206505-4	1-206505-4
	.120 [3.05]	570566-5	1-206505-3	1-206505-3
	.120 [3.05]	LMSC 1621480-006	1-206505-2	1-206505-2
	.120 [3.05]	LMSC 1621480-006	1-206505-1	1-206505-1
	.120 [3.05]	311P407-5S-B-12	206505-4	1-206505-0
	.120 [3.05]	20025720P1078S	206505-9	206505-9
	.120 [3.05]	R4383P78S	206505-8	206505-8
	.154 [3.91]		206505-7	206505-7
	.120 [3.05]	R4383P78S-2	206505-6	206505-6
	.120 [3.05]	SC81D139-045	206505-5	206505-5
	.120 [3.05]	311P407-5S-B-12	206505-4	206505-4
	.154 [3.91]		206505-3	206505-3
	.120 [3.05]	R9259P78S	206505-2	206505-2
	.154 [3.91]	311P407-5S-B-15	206505-1	206505-1
REMARKS	DIA A	CUSTOMER P/N ON CONNECTOR	AMP P/N ON CONNECTOR	AMP P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN M. CLOUSER 12-16-98 CDE 1-24-89 T. CANTLIN 1-25-89 F. KINSEY PRODUCT SPEC APPLICATION SPEC		 TE Connectivity	
DIMENSIONS: INCHES  0 PLC ± . 1 PLC ± . 2 PLC ± . 3 PLC ± .005 [0.13] 4 PLC ± .1* ANGLES FINISH		TOLERANCES UNLESS OTHERWISE SPECIFIED: SEE CALLOUTS		NAME AMPLIMITE NONMAGNETIC RECEPTACLE ASSEMBLY, SERIES 90, SHELL SIZE 5, 78 POSITION	
MATERIAL SEE CALLOUTS		WEIGHT —		SIZE A1	
		CUSTOMER DRAWING		CAGE CODE 00779	
				DRAWING NO C=206505	
				RESTRICTED TO SCALE 4:1 SHEET 1 OF 1 REV Y	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[311P407-5S-B-15](#)