




P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	15MAR11	RK	MKO

- NOTE:
- 1
- HOUSING: GLASS FILLED THERMOPLASTIC
CONTACTS: COPPER ALLOY
- 2
- PLATING:
CONTACT AREA: PERFORMANCE LEVEL 2 ACC. TO DIN 41612
SOLDERING AREA: TIN OVER NICKEL
- 3
- CONTACT ARRANGEMENTS:
AN ASTERISK "X" DENOTES A SIGNAL CONTACT.
AN ASTERISK "⊗" DENOTES KINKED A SIGNAL CONTACT.
- 4
- KINKED POSTS
5.
- SOLDER POSTS SUITABLE FOR 1,0 NOM. P.C.B. HOLES
6.
- CONNECTOR PRINTED WITH PARTNUMBER AND DATECODE



POS		3																															
ROW		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	32
	a	⊗	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	⊗
	b	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○
c		⊗	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	⊗

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISH -

DWN
RAVINDRA K
15MAR11

CHK
MARCIN KOMAR
07APR11

APVD
STEFAN HABERSTROH
07APR11

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

WITH
4

2
FINISH

1
MATERIAL

2173046-4
TE PARTNUMBER

TE Connectivity

NAME
64P.IEC-C FEM.CONN.
ACC. DIN 41612 WITH SOLDER POSTS
2,4 - 3,2mm P.C.BOARD THICKNESS

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=2173046

RESTRICTED TO
-

SCALE
NTS

SHEET
1 OF 1

REV
A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2173046-4](#)