


| LOC | DIST | REVISIONS |     |                           |         |     |      |
|-----|------|-----------|-----|---------------------------|---------|-----|------|
|     |      | P         | LTR | DESCRIPTION               | DATE    | DWN | APVD |
| AJ  | 16   |           | C   | REVISED PER 0S14-0355-03. | 31DEC03 | JGH | JGH  |
|     |      |           |     |                           |         |     |      |



1. BERYLLIUM COPPER PER ASTM-B-197.
2. GOLD PLATE PER MIL-G-45204, 0.76µm [.000030] MIN THICKNESS.
3. SILVER PLATE PER QQ-S-365, 2.54µm [.000100] MIN THICKNESS.
4. TIN-LEAD PLATE PER ASTM-B-545, 2.54µm [.000100] MIN THICKNESS.

|             |        |             |
|-------------|--------|-------------|
| 1.22 [.048] | 2      | 3-221149-6  |
| 0.41 [.016] | 2      | 3-221149-1  |
| 1.14 [.045] | 2      | 2-221149-6  |
| 0.64 [.025] | 3      | 2-221149-1  |
| 0.64 [.025] | 2      | 2-221149-0  |
| 0.64 [.025] | 4      | 1-221149-9  |
| 0.81 [.032] | 3      | 1-221149-4  |
| 0.81 [.032] | 2      | 1-221149-3  |
| 0.81 [.032] | 4      | 1-221149-2  |
| 1.07 [.042] | 3      | 221149-7    |
| 1.07 [.042] | 2      | 221149-6    |
| 1.07 [.042] | 4      | 221149-5    |
| A           | FINISH | PART NUMBER |

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:  
mm [INCHES]

MATERIAL  
SEE NOTES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-  
1 PLC ±-  
2 PLC ±-  
3 PLC ±-  
4 PLC ±-  
ANGLES ±-

FINISH  
SEE TABLE

DWN  
MICHAEL E. COWHER  
12JAN96

CHK  
MICHAEL J. PHILLIPS  
15JAN96

APVD  
MICHAEL J. PHILLIPS  
15JAN96

PRODUCT SPEC  
—

APPLICATION SPEC  
—

WEIGHT  
—

CUSTOMER DRAWING

AMP

AMP Incorporated  
Harrisburg, PA 17105-3608

NAME  
CONTACT, JACK, COMMERCIAL, BNC

SIZE  
A3

CAGE CODE  
00779

DRAWING NO  
C-221149

SCALE  
10:1

SHEET  
1 OF 1

REV  
C

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-221149-6](#)