



S



PART N <sup>o</sup>	COLOR
229909-1	BLK
229909-4	GRAY

LTR	REVISION RECORD	DR	CHK	DATE
F	035-Z EENAA-3065	SD	1/24/80	
E	DESOLETE-3, PER ECN AA-2584	JW	SD	9-18-80
D	INACTIVATE-2-3 PER ECNAA-274	CU	SD	2/2/84
C	ADDED (-4) ECUC-81	RR	SD	9/11/82
B	ADDED (-3) ECN C-3Y	JC	SD	4-21-72
A	ADDED (-2)	JC	SD	4-2-72

NUMBER	REQUIRED PER ASSEMBLY	DESCRIPTION
229909		

DWG SIZE	UNPUBLISHED COPY NOT TO BE REPRODUCED NOR PUBLISHED WITHOUT WRITTEN PERMISSION OF AMP INCORPORATED		REMARKS		ITEM NO
DR	JEC	11-22-71	CUSTOMER COPY REFERENCE ONLY		
CHK			AMP INCORPORATED HARRISBURG, PENNA.		
DE	THERMOPLASTIC		CLASS		
WIRE - RANGE - INSULATION		TYPE			
TOLERANCE EXCEPT AS NOTED ± .015 ± 1" 0'		SCALE		LOC AA	NO 229909
NAME		COVER		REV F	
50 POSITION CHAMP® CONNECTOR					

DIMENSIONS IN INCHES. DO NOT SCALE PRINT

10/2 AA

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[229909-4](#)