




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW DRAWING	21JAN2016	NK	RH



- 1
- WORKING TEMPERATURE: 105° C
- 2
- VOLTAGE: 300V/600V MAX
- 3
- COLOR: RED
- 4
- WIRE RANGE: #22-#10AWG MAX.2#10
SOL W/2#12 STR MIN.3#18
- 5
- SPRING INSERT: STEEL

2299504-1 AS SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN NAGALAKSHMI K 21JAN2016	 TE Connectivity							
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK HILL RYAN 21JAN2016	NAME CPGI-WC-WG-RD-BULK							
		APVD HILL RYAN 21JAN2016								
	0 PLC ± - 1 PLC ± 0.2[.007] 2 PLC ± 0.4[.015] 3 PLC ± - 4 PLC ± - ANGLES ± -	PRODUCT SPEC -	SIZE A3			CAGE CODE 00779	DRAWING NO C-2299504	RESTRICTED TO -		
		APPLICATION SPEC -								
		MATERIAL TOUGH THERMOPLASTIC UL 94V-2 FLAME-RETARDANT	FINISH -	WEIGHT -	CUSTOMER DRAWING					SCALE 3:1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2299504-1](#)