





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW DRAWING	14JAN2016	NK	RH



- 1
- WORKING TEMPERATURE: 105° C
- 2
- VOLTAGE: 600V MAX.
- 3
- COLOR: TAN
- 4
- WIRE RANGE: #22-#8 AWG MAX.4#12
MIN.3#22 SOL
- 5
- SPRING INSERT: STEEL

2299510-1 AS SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN NAGALAKSHMI K 14JAN2016	 TE Connectivity						
		CHK HILL RYAN 14JAN2016							
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD HILL RYAN 14JAN2016	NAME CPGI-WC-TG-TN-BULK						
	0 PLC ± - 1 PLC ± 0.2[.007] 2 PLC ± 0.4[.015] 3 PLC ± - 4 PLC ± - ANGLES ± -	PRODUCT SPEC —							
		APPLICATION SPEC —	SIZE A3	CAGE CODE 00779	DRAWING NO C-2299510	RESTRICTED TO —			
	MATERIAL TOUGH THERMOPLASTIC UL 94V-2 FLAME-RETARDANT	FINISH —	WEIGHT —	CUSTOMER DRAWING				SCALE 2:1	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2299510-1](#)