


LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION	DATE	OWN	APP		
L1		DRAWING MAINTENANCE	12-16-05	JDM	MKS		

CODE
CDM 032-0025-0001

CABLE ACCEPTANCE DIMS.
JACKET D. ————.093 MAX.
DIELECTRIC D. ————.050 MAX.
CENTER CONDUCT. D. ————.013 MAX.



003-0270-0000	B.R. CAP	SILICONE RUBBER ZZ-R-165	7
003-0597-0001	SLEEVE	TEFLON PER L-P-403	6
005-2319-0001	RING	BRASS PER QQ-B-626	5
003-0326-0001	FERRULE	BRASS PER QQ-B-626	4
003-0029-0001	NUT	BRASS PER QQ-B-626	3
003-0027-0001	BUSHING	TEFLON PER L-P-403	2
003-0359-0002	PIN	BRASS PER QQ-B-626	1
COMPONENT NOMENCLATURE		MAT'L & SPEC	ITEM
NO			NO.

- 8 MALE DIAMOND KNURL
7 150-32 UNF-2B THREAD.
6 GOLD PLATE .00005 MIN. PER MIL-G-45204 TYPE II, CLASS I
5 SILVER PLATE .0002-.0004 PER QQ-S-365
4 DELETED
3. MALCO ASSY TOOL #T-3221 OR 010-0003-0000 REQD.
2. FOR ASSY INSTRUCTIONS SEE RF-ASMB-88.
1. THIS CONNECTOR MATES WITH ALL S-50 JACKS AND RECEPTACLES AS LISTED IN MALCO CATALOG
- NOTES: UNLESS OTHERWISE SPECIFIED

L1		SEE TYCO TITLE BLOCK	
1-40871		UPDATE REV LETTER	
ASSEMBLY	NO REQ'D	PL 3-1	OR
NEXT ASSEMBLIES	LET EGO	DATE	APP

STANDARD TOLERANCES UNLESS OTHERWISE SPECIFIED DEC. IS .010 FRACTION 1/32 ANGLE 1/2 ECCENTRICITY MAX. TYP. HOLE DIA. ± .001 SURFACE ROUGHNESS MICRO INCHES THREADS TO MIL-STD-208 COMMERCIAL TOLERANCES APPLY TO STOCK DIMENSIONS		MICRODOT INC. SOUTH PASADENA, CALIF.	
SURFACE TREATMENT NOTED		MATERIAL NOTED	
DRAWN BY M.F.M.		APP G.R.F.	
PROO CODE 931		SCALE 1/1	
CODE CDM		DRAWING NUMBER 032-0025-0001	

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN D. MORALES 12-16-05	12-16-05
DIMENSIONS: INCHES		CHK M. STORRY 12-16-05	12-16-05
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1/32 1 PLC ± 2 PLC ± 3 PLC ± .010 4 PLC ± ANGLES ±		NAME M. STORRY	12-16-05
MATERIAL FINISH		PRODUCT SPEC	
APPLICATION SPEC		SIZE A2	98278
WEIGHT		CASE CODE C-3	1532004-5
CUSTOMER DRAWING		RESTRICTED TO	
SCALE NONE		SHEET 1 of 1	REV 1.1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[032-0025-0001](#)