






CONTACT DIMENSIONS




RECOMMENDED PCB-HOLE LAY-OUT

COMPONENT SIDE SHOWN



CONTACT LAYOUT



NOTES:

-  MATERIAL HOUSING : GREY GLASS FILLED POLYESTER
 : UL-RATING V0
 CONTACT : PHOSPHORBRONZE
-  GENERAL CONTACT PLATING SPECIFICATION: UNDERPLATING (ENTIRE CONTACT):
 1,27μm NICKEL MIN. AND ACTION PIN: 0,5μm TIN-LEAD MIN.
 FOR PLATING OF MATING SURFACES SEE APPLICABLE SPECIFICATION
 REFERENCE FOR EACH DASH NUMBER.
 REDUCED CROSS-TALK SHIELD: GOLD FLASH OVER 1,27μm NICKEL MIN.
-  CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101
 PERFORMANCE LEVEL 2.
-  CONNECTOR ASSEMBLY WITH LATCH HINGE FOR CABLE CONNECTOR.
-  CONNECTOR PRINTED WITH PARTNUMBER AND DATECODE
-  PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID.
-  PLATED SPOT ONLY ON COMPONENT SIDE, FORMING ONE CONTACT
 WITH PLATED THROUGH HOLES OF ROW C

P.C.B. HOLE DIM. ACTION PIN FIN. HOLE : 0,55 TO 0,65mm OTHER REQUIREMENTS SEE APPLICATION SPECIFICATION

LOC	DIST	REVISIONS					
H	—	P	LTR	DESCRIPTION	DATE	DWN	APVD
			D	EH10-0680-05	06-06-05	BSV	BM
			D1	ECR-06-002635	07-02-06	BSV	BM
			E	ECR-06-026577	14-11-06	BSV	BM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L.V.D.HEJWEN 12FEB98		 Tyco Electronics Corporation s-HertogenBosch, Netherlands,	
DIMENSIONS: mm		CHK D.TRUREN 12FEB98		NAME	
		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH		F.V.KONINGSBRUGGE PRODUCT SPEC 108-19082 APPLICATION SPEC 114-19029 WEIGHT -	
MATERIAL -		Z-PACK 2MM HM TYPE C 55 POS. RIGHT ANGLE MALE CONNECTOR WITH REDUCED CROSS-TALK SHIELDS		SIZE A2	RESTRICTED TO -
		CAGE CODE 00779		DRAWING NO C-352273	
CUSTOMER DRAWING				SCALE NTS	SHEET 1 OF 1
				REV F	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-352273-1](#)